



Specification

1.06609.0000 Sodium peroxodisulfate for analysis EMSURE®

Specification		
Assay (iodometric)	≥ 99.0	%
Identity	passes test	
Chloride (Cl)	≤ 0.01	%
Heavy metals (as Pb)	≤ 0.003	%
NH ₄ (Ammonium)	≤ 0.05	%
Cr (Chromium)	≤ 0.001	%
Cu (Copper)	≤ 0.001	%
Fe (Iron)	≤ 0.0005	%
Mn (Manganese)	≤ 0.0001	%
Pb (Lead)	≤ 0.001	%
Loss on drying (105 °C; 3 hours)	≤ 0.05	%

Dr. Dimitrij Ryvlin

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.