

Dulbecco's Phosphate Buffered Saline

| Component | D1283 | D1408 | D4031 | D5652 | D5773 | D8537 | D8662 |
|------------------------------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|
| | [Liquid] g/L | [Liquid] g/L | [Liquid] g/L | [Powder] g/L | [Powder] g/L | [Liquid] g/L | [Liquid] g/L |
| Inorganic salts | | | | | | | |
| CaCl ₂ • 2H ₂ O | 1.33 | — | 0.133 | — | — | — | 0.133 |
| MgCl ₂ • 6H ₂ O | 1 | — | 0.1 | — | 0.1 | — | 0.1 |
| KCl | 2 | 2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| KH ₂ PO ₄ | 2 | 2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| NaCl | 80 | 80 | 8 | 8 | 8 | 8 | 8 |
| Na ₂ HPO ₄ (anhyd) | 11.5 | 11.5 | 1.15 | 1.15 | 1.15 | 1.15 | 1.15 |
| Sugars | | | | | | | |
| D-Glucose | — | — | 1 | — | — | — | — |
| Kanamycin sulfate | — | — | 0.1 | — | — | — | — |
| Pyruvic acid • Na | — | — | 0.036 | — | — | — | — |
| Streptomycin sulfate | — | — | 0.05 | — | — | — | — |