

## M2 and M16 Media

Component	M16 <a href="#">M7292</a> [Liquid] g/L	M2 <a href="#">M7167</a> [Liquid] g/L
<u>Inorganic salts</u>		
CaCl <sub>2</sub> • 2H <sub>2</sub> O	0.251	0.251
MgSO <sub>4</sub> (anhyd)	0.165	0.165
KCl	0.356	0.356
KH <sub>2</sub> PO <sub>4</sub>	0.162	0.162
NaHCO <sub>3</sub>	2.101	0.35
NaCl	5.532	5.532
<u>Sugars</u>		
D-Glucose	1	1
<u>Other</u>		
Albumin, bovine Fraction V	4	4
Lactic acid • Na	2.95	2.95
Phenol red • Na	0.01	0.01
Pyruvic acid • Na	0.036	0.036
HEPES	—	5.43