

Product Information

EPINEPHRINE BITARTRATE SIGMA REFERENCE STANDARD

Product No. **E1016**

Lot No: 124K8803


Storage Temperature: 2° - 8°

Formula: C₉H₁₃NO₃ • C₄H₆O₆

Formula Weight: 333.29

CAS No: 51-42-3

Synonyms: 1,2-Benzenediol, 4-[1-hydroxy-2-(methylamino)ethyl]-, (*R*)-, [*R*-(*R*^{*}, *R*^{*})]-2,3-dihydroxybutanedioate (1:1) (salt).
 (-)-3,4-Dihydroxy- α -[(methylamino)methyl]benzyl alcohol
 (+)-tartrate (1:1) (salt).



Product Description

This product meets USP specifications (Current through USP 28), and is traceable to USP Reference Standard lot O

Store in sealed vial at refrigerator temperature. Protect from light. Dry a portion in vacuum over silica gel for 3 hours before using. Use promptly. Discard unused material.

TEST	USP 28 SPECIFICATIONS	Result Sigma R.S. Lot 124k8803
Identification	a deep red color is produced	passes
Melting range °C (741)	between 147° and 152°	151-152°
Loss on Drying (731)	not more than 0.5%	passes
Residue on ignition (281)	negligible from 100 mg	passes
Limit of anderalone (851)	absorptivity at 310 nm not more than 0.2	passes
Limit of norepinephrine	not more than 4.0%	passes
Assay	not less than 97.0% and not more than 102.0%	99.8%

THIS PAGE DELIBERATELY LEFT BLANK

12/2004

Sigma brand products are sold through Sigma-Aldrich, Inc.
Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications.
Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply.
Please see reverse side of the invoice or packing slip.