



Restricted Use License

This Restricted Use License sets out the terms and conditions under which certain Reprogramming Kits ("Products") are being provided to Recipient ("Licensee") by Stemgent Inc. pursuant to a license agreement between Stemgent Inc. and the Whitehead Institute.

1. Products are for basic research use only by the Licensee and only pursuant to the terms of this license agreement. LICENSEE SHALL USE THE PRODUCTS SOLELY FOR THE PURPOSE OF CONDUCTING INTERNAL, NONCOMMERCIAL RESEARCH. PURCHASER WILL NOT SELL, TRANSFER, DISCLOSE OR OTHERWISE PROVIDE ACCESS TO THE PRODUCTS OR ANY DESCENDENTS/PROGENY TO ANY PERSON OR ENTITY.

2. Licensee understands that the Products, under certain circumstances, may have biological and/or chemical properties that are unpredictable and unknown at the time of transfer, that they are to be used with caution and prudence, and are not to be used for testing in or treatment of humans or animals.

This product is intended for basic research purposes only including without limitation basic research having as its primary purpose understanding the biology or pathology of cells or cell lines and diseases or disorders affecting them. It may not be used for (i) any human clinical use or veterinary use including without limitation therapeutic, prophylactic or diagnostic use, (ii) discovery, development, or manufacturing of pharmaceutical products (including without limitation assay development or cell line generation for drug discovery or drug development, screening of chemical and/or biological compounds for the identification of pharmaceutically active agents, or preclinical testing, or services related to the above), or (iii) conducting services for the purpose of discovering or developing pharmaceutical products. Further, this product may not be used to manufacture or as part of or for any commercial products or services, other than performing basic research as described above on behalf of others. This product may not be resold, redistributed or transferred.

Any use of this product for any of the above-mentioned purposes requires a license from the Whitehead Institute or one of its licensees, and the Whitehead Institute and its exclusive licensees will be express third-party beneficiaries of the foregoing restrictions. The foregoing restrictions amount to a restricted license under applicable patent and other intellectual property rights.

3. The Products are provided under at least one of the following patents and related filings:

- U.S. Patent Appl. Nos. 10/997,146
- U.S. Provisional Appl. No 61/036

4. Title to the Products shall not transfer to the Licensee.

5. EXCEPT AS EXPRESSLY PROVIDED HEREIN, STEMGENT INC. DISCLAIMS ALL REPRESENTATIONS AND WARRANTIES OF ANY KIND, EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION, ANY WARRANTY OF NON-INFRINGEMENT, TITLE, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

6. IN NO EVENT SHALL STEMGENT INC. BE LIABLE FOR ANY SPECIAL, INCIDENTAL, CONSEQUENTIAL OR PUNITIVE DAMAGES IN CONNECTION WITH THIS RESTRICTED USE LICENSE AGREEMENT OR THE LICENSE GRANTED HEREUNDER.

7. This Agreement shall commence upon opening of the packaging (the "Effective Date"), and continue until the Products are used in accordance with Section 1. Upon termination of this Agreement, no Products or descendents or progeny shall remain in Licensee's possession.



Restricted Use License

8. This Agreement with respect to the subject matter hereof (i) sets forth the complete and entire agreement of the parties; and (ii) supersedes and terminates all prior agreements and understandings between the parties. No subsequent amendment or addition to this Agreement shall be binding upon the parties hereto unless reduced to writing and signed by the respective authorized officers of the parties. This Agreement shall not be assigned or otherwise transferred by Licensee.

9. This Agreement shall be governed by, and construed and enforced in accordance with, the laws of the State of Delaware.

For more information or questions relating to the permitted uses and the recommended protocol for the Products, please direct all inquiries to:

Stemgent, Inc.
790 Memorial Drive
Cambridge, MA 02139
Tel: 617-245-0000
Website: www.stemgent.com

Use of the Tetracycline controllable expression systems (the "Tet Technology") is covered by a series of patents including U.S. patents # 5,464,758 and #5,814,618, which are proprietary to TET Systems Holding GmbH & Co. KG. Academic research institutions are granted an automatic license with the purchase of this product to use the Tet Technology only for internal, academic research purposes, which license specifically excludes the right to sell, or otherwise transfer, the Tet Technology or its component parts to third parties. Notwithstanding the above, academic and not-for profit research institutions whose research using the Tet Technology is sponsored by for profit organizations, which shall receive ownership to all data and results stemming from the sponsored research, shall need a commercial license agreement from IP Merchandisers in order to use the Tet Technology. In accepting this license, all users acknowledge that the Tet Technology is experimental in nature. TET Systems Holding GmbH & Co. KG makes no warranties, express or implied or of any kind, and hereby disclaims any warranties, representations, or guarantees of any kind as to the Tet Technology, patents, or products. All others are invited to request a license from TET Systems Holding GmbH & Co. KG prior to purchasing these reagents or using them for any purpose. Stemgent Inc. is required by its licensing agreement to submit a report of all purchasers of the Tet-controllable expression system to IP Merchandisers, Inc. For license information, please contact:

TET Systems Holding GmbH & Co. KG
Attn. CEO
Im Neuenheimer Feld 582
69120 Heidelberg
Germany
Tel: +49 6221 588 04 00
Fax: +49 6221 588 04 04