


Product Specification

Product Name :	Doxycycline hyclate Suitable for Cell Culture
Product Number:	D5207
CAS Number:	24390-14-5
MDL Number :	MFCD07357237
Storage Temperature :	+2°C to +8°C
Molecular Formula:	$C_{22}H_{24}N_2O_8 \cdot HCl \cdot 0.5H_2O \cdot 0.5C_2H_6O$
Formula Weight:	512.94 g/mol



Test	Specification
Appearance (Color) Yellow to Yellow-Green	Conforms
Appearance (Form) Powder	Conforms
Assay (EP) (anhydrous, Ethanol free based)	95.0 - 102.0 %
Results Provided by Supplier	-----
Suitability	Pass
Tested by Releasing Site	-----
Shelf Life Defined by Supplier	-----
Handled & Packed Under ISO9001	-----

Sigma-Aldrich warrants that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

Version Number: PRP.00.ZQ5.1142814

Page 1 of 1

The branding on the header and/or footer of this document may temporarily not visually match the product purchased as we transition our branding. However, all of the information in the document regarding the product remains unchanged and matches the product ordered. For further information please contact mlsbranding@sial.com

