



Product Information

SIGMA QUALITY CONTROL TEST PROCEDURE

Enzymatic Assay of TREHALASE (EC 3.2.1.28)

PRINCIPLE:



CONDITIONS: T = 37 °C, pH = 5.7, $A_{340\text{nm}}$, Light path = 1 cm

METHOD: Spectrophotometric Stop Rate Determination

REAGENTS:

- A. 135 mM Citric Acid Buffer, pH 5.7 at 37 °C
(Prepare 100 ml in deionized water using Citric Acid, Free Acid, Monohydrate, Product No. C 7129. Adjust to pH 5.7 at 37 °C with 1 M NaOH.)
- B. 140 mM D-Trehalose Solution
(Prepare 10 ml in Reagent A using D(+)-Trehalose, Dihydrate, Product No. T 5251.)
- C. 500 mM Tris Buffer, pH 7.5 at 37 °C
(Prepare 100 ml in deionized water using Trizma Base, Product No. T 1503. Adjust to pH 7.5 at 37 °C with 1 M HCl.)
- D. Trehalase Enzyme Solution
(Immediately before use, prepare a solution containing 0.1 - 0.3 unit/ml of Trehalase in cold Reagent A.)
- E. Glucose Determination Vial
(Use Stock No. 16-10, Glucose (HK) 10 Reagent. Dissolve the contents in 10 ml of deionized water.)

**Enzymatic Assay of TREHALASE
(EC 3.2.1.28)**

PROCEDURE:

Step 1:

Pipette (in milliliters) the following reagents into suitable cuvettes:

	<u>Test</u>	<u>Blank</u>
Reagent A (Citrate Buffer)	0.3	0.3
Reagent D (Enzyme Solution)	0.1	0.1

Mix by inversion and equilibrate to 37 °C using a suitably thermostatted spectrophotometer. Then add:

Reagent B (D-Trehalose)	0.1	-----
-------------------------	-----	-------

Immediately mix by inversion and incubate at 37 °C for exactly 15 minutes. Then add:

Reagent C (Tris Buffer)	0.5	0.5
Reagent B (D-Trehalose)	-----	0.1

Step 2:

Pipette (in milliliters) the following reagents into suitable cuvettes:

	<u>Test</u>	<u>Blank</u>
Reagent E (16-10)	3.0	3.0

Equilibrate to 37 °C. Monitor the $A_{340\text{nm}}$ until constant, using a suitably thermostatted spectrophotometer. Record the initial $A_{340\text{nm}}$ for both Test and Blank. Then add:

Test Solution	0.1	-----
Blank Solution	-----	0.1

Immediately mix by inversion and record the increase in $A_{340\text{nm}}$ until complete (approximately 5 minutes). Obtain the final $A_{340\text{nm}}$ for both the Test and Blank.

**Enzymatic Assay of TREHALASE
(EC 3.2.1.28)**

CALCULATIONS:

$$\Delta A_{340\text{nm}} \text{ Test} = A_{340\text{nm}} \text{ Test Final} - A_{340\text{nm}} \text{ Test Initial}$$

$$\Delta A_{340\text{nm}} \text{ Blank} = A_{340\text{nm}} \text{ Blank Final} - A_{340\text{nm}} \text{ Blank Initial}$$

$$\text{Units/ml enzyme} = \frac{(\Delta A_{340\text{nm}} \text{ Test} - \Delta A_{340\text{nm}} \text{ Blank})(1.0)(3.1)}{(6.22)(2)(15)(0.1)(0.1)}$$

6.22 = Millimolar extinction coefficient of β -NADH at 340nm
2 = Number of Glucose molecules per molecule of Trehalose
15 = Reaction time (in minutes) of Step 1
1.0 = Final volume (in milliliters) of Step 1
3.1 = Final volume (in milliliters) of Step 2
0.1 = Volume From Step 1 used in Step 2
0.1 = Volume (in milliliters) of enzyme used

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

One unit will convert 1.0 μ mole of trehalose to 2.0 μ moles of glucose per minute at pH 5.7 at 37 °C (liberated glucose determined at pH 7.5).

FINAL ASSAY CONCENTRATION:

In a 0.50 ml reaction mix, the final concentrations are 135 mM citric acid, 28 mM D-trehalose, and 0.01 - 0.03 unit of trehalase.

REFERENCE:

Dahlqvist, A. (1968) *Analytical Biochemistry* **22**, 99-107

NOTES:

1. This assay is based on the cited reference.
2. Where Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.