



**DONKEY ANTI-GOAT IGG
AFFINITY PURIFIED, FLUORESCHEIN CONJUGATED
ABSORBED FOR DUAL LABELING
SECONDARY ANTIBODY**

CATALOG NUMBER:	AP180F
LOT NUMBER:	
QUANTITY:	500 µg
SPECIFICITY:	Goat IgG
FLUOROPHORE/ PROTEIN:	Approximately 8.2 µg/mg.
WAVELENGTH:	Absorption peak = 492 nm, Emission peak = 520 nm.
APPLICATIONS:	Suggested dilution for most applications: 1:50-1:200 Optimal working dilutions must be determined by end user.
FORMAT:	Affinity purified donkey immunoglobulin conjugated to fluorescein. The antibody is isolated from antisera by immunoaffinity chromatography using antigen coupled to agarose beads. The antibody has been absorbed against human, rat, rabbit, horse, guinea pig, hamster, chicken and mouse to minimize naturally occurring cross-reactivities.
PRESENTATION:	Lyophilized. Buffer = 0.01 M Sodium Phosphate, 0.25 M NaCl, pH 7.6 with 15 mg/mL BSA, and 0.5% sodium azide.
RECONSTITUTION:	Reconstitute with 500 µL of sterile distilled water.
STORAGE/HANDLING:	Maintain lyophilized product at 2-8°C for up to 12 months. After reconstitution the product is stable for several weeks at 2-8°C as an undiluted liquid. For extended storage after reconstitution, add an equal volume of glycerol (ACS grade or better) to make a final concentration of 50% glycerol followed by storage at -20°C in undiluted aliquots for up to 12 months. Please note the concentration of protein (and buffer salts) will decrease to one-half of the original after the addition of glycerol. Avoid repeated freeze/thaw cycles.
Important Note:	<i>During shipment, small volumes of product will occasionally become entrapped in the seal of the product vial. For products with volumes of 200 µL or less, we recommend gently tapping the vial on a hard surface or briefly centrifuging the vial in a tabletop centrifuge to dislodge any liquid in the container's cap.</i>

**FOR RESEARCH USE ONLY; NOT FOR USE IN DIAGNOSTIC
PROCEDURES. NOT FOR HUMAN OR ANIMAL CONSUMPTION**

Unless otherwise stated in our catalog or other company documentation accompanying the product(s), our products are intended for research use only and are not to be used for any other purpose, which includes but is not limited to, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses or any type of consumption or application to humans or animals.

©2002 - 2010: Millipore Corporation. All rights reserved. No part of these works may be reproduced in any form without permission in writing.

28820 Single Oak Drive • Temecula, CA 92590
Technical Support: T: 1-800-MILLIPORE (1-800-645-5476) • F: 1-800-437-7502
www.millipore.com