




Product Information

SIGMA QUALITY CONTROL TEST PROCEDURE

Enzymatic Assay of XANTHINE OXIDASE (EC 1.1.3.22)

PRINCIPLE:



CONDITIONS: T = 25°C, pH = 7.5, A_{290nm}, Light Path = 1 cm

METHOD: Continuous Spectrophotometric Rate Determination

REAGENTS:

- A. 50 mM Potassium Phosphate Buffer, pH 7.5 at 25°C
(Prepare 200 ml in deionized water using Potassium Phosphate, Monobasic, Anhydrous, Sigma Prod. No. P-5379. Adjust to pH 7.5 at 25°C with 1 M KOH.)
- B. 0.15 mM Xanthine Solution
(Prepare 100 ml by initially dissolving Xanthine, Sigma Prod. No. X-0626, in a minimal volume of NaOH. Add approximately 90 ml of deionized water. Adjust to pH 7.5 at 25°C with either 1 M NaOH or 1 M HCl. Dilute to a final volume of 100 ml. **PREPARE FRESH.**)
- C. Xanthine Oxidase Enzyme Solution
(Immediately before use, prepare a solution containing 0.1 - 0.2 unit/ml of Xanthine Oxidase in cold Reagent A.)

PROCEDURE:

Pipette (in milliliters) the following reagents into suitable quartz cuvettes:

	<u>Test</u>	<u>Blank</u>
Reagent A (Buffer)	1.90	1.90
Reagent B (Xanthine)	1.00	1.00
Deionized Water	-----	0.10

Enzymatic Assay of XANTHINE OXIDASE (EC 1.1.3.22)

PROCEDURE: (continued)

Mix by inversion and equilibrate to 25°C. Monitor the $A_{290\text{nm}}$ until constant, using a suitably thermostatted spectrophotometer. Then add:

	<u>Test</u>	<u>Blank</u>
Reagent C (Enzyme Solution)	0.10	-----

Immediately mix by inversion and record the increase in $A_{290\text{nm}}$ for approximately 5 minutes. Obtain the $\Delta A_{290\text{nm}}/\text{minute}$ using the maximum linear rate for both the Test and Blank.

CALCULATIONS:

$$\text{Units/ml enzyme} = \frac{(\Delta A_{290\text{nm}}/\text{min Test} - \Delta A_{290\text{nm}}/\text{min Blank})(3)(\text{df})}{(12.2)(0.1)}$$

3 = Total volume (in milliliters) of assay

df = Dilution factor

12.2 = Millimolar extinction coefficient of Uric Acid at 290 nm

0.1 = Volume (in milliliter) of enzyme used

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/ml enzyme}}$$

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

One unit will convert 1.0 μmole of xanthine to uric acid per minute at pH 7.5 at 25°C.

FINAL ASSAY CONCENTRATION:

In a 3.00 ml reaction mix, the final concentrations are 33 mM potassium phosphate, 0.050 mM xanthine and 0.01 - 0.02 unit xanthine oxidase.

Enzymatic Assay of XANTHINE OXIDASE (EC 1.1.3.22)

REFERENCE:

Bergmeyer, H.U., Gawehn, K. and Grassl, M. (1974) in *Methods of Enzymatic Analysis* (Bergmeyer, H.U. ed.) Second Edition, Volume I, 521-522, Academic Press Inc., New York, NY

NOTES:

1. This assay is based on the cited reference.
2. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.