

# TagGFP2 Simplicon™ Plasmid (E3L)

Plasmid DNA

Cat. # SCR725

FOR RESEARCH USE ONLY.  
NOT FOR USE IN DIAGNOSTIC PROCEDURES.  
NOT FOR HUMAN OR ANIMAL CONSUMPTION.

Pack size: 10 µg

Store at -20 °C



Data Sheet

page 1 of 2

## Background

Simplicon™ is a novel system to effect immediate high sustained protein expression of multiple genes into transfected cells without the risk of genome integration. The technology employs a single, synthetic, polycistronic, self-replicating RNA based on the Venezuelan equine encephalitis (VEE) genome<sup>1,2,3,4</sup>. The Simplicon™ RNA contains only genes encoding the VEE RNA replication machinery while the structural proteins that are required to make an infectious particle have been removed and replaced with the transgenes of interest. The Simplicon™ RNA is a synthetic RNA generated from the Simplicon™ Cloning Vector (E3L) plasmid.

Introduction and replication of the Simplicon™ RNA is expected to elicit a strong interferon response in transfected cells. To suppress the IFN responses, a Vaccinia virus protein<sup>5</sup>, B18R, is used for the original Simplicon™ technology. Recently, we found that another Vaccinia virus protein<sup>5</sup>, E3L, also suppresses the IFN responses in Simplicon™ RNA expression. B18R neutralizes type I interferons by direct binding, while E3L inhibits the cytoplasmic signaling pathways of IFN responses. Therefore, B18R and E3L are both employed in the Simplicon™ Expression System and work collaboratively to suppress IFN responses. As a result, there is increased cell viability during RNA transfection and increased expression of the transgenes. The Simplicon™ Expression System works in human cells and is not expected to work in mouse cells. This is because the B18R does not effectively neutralize mouse interferon (IFN)-β.

One day after transfection of the Simplicon™ RNA, a spike in the levels of transgenes can be observed. The expression levels are maintained by addition of B18R, E3L and the selective agent, puromycin throughout the duration of the experiment. Over time, expression levels are expected to diminish and stabilize to 1/5 – 1/10 the levels initially observed and may be close to physiological levels after one week. Expression levels and duration may change depending upon the cell types, transgenes and media conditions used. The Simplicon™ technology has been successfully utilized for efficient human iPSC generation through the sustained expression of critical reprogramming factors<sup>3,4</sup> and in the creation of cell lines that express and retain the metabolic activities of five cytochrome P450 enzymes<sup>6</sup>.

In the Simplicon™ Expression System, B18R and E3L are provided as a B18R-E3L RNA (Cat. No. SCR722) for the suppression of IFN responses at RNA transfection. For sustained transgene expression, recombinant B18R protein (Cat. No. SCR156 and SCR197) or B18R conditioned medium (B18R-CM) can be used. E3L is continuously provided from the Simplicon™ RNA itself. B18R-CM can be produced

from B18R-E3L RNA or B18R RNA synthesized using the B18R-E3L plasmid (Cat. No. SCR727) or B18R plasmid (Cat. No. SCR728), respectively.

The TagGFP2 Simplicon™ Plasmid (E3L) was developed for the synthesis of TagGFP2 Simplicon™ RNA (E3L). The Simplicon™ TagGFP2 RNA may be used to determine optimal transfection conditions to express the self-replicating RNA in hard-to transfect somatic or primary cells. Simplicon™ TagGFP2 expresses an improved variant of the *Aequorea macrodactyla* GFP-like protein. TagGFP2 exhibits bright green fluorescence comparable to that of EGFP, with excitation/emission maxima at 483 and 506 nm, respectively<sup>7,8</sup>.

## Plasmid Information

Plasmid map is indicated on the next page. Full DNA sequence data is available on our website ([www.emdmillipore.com](http://www.emdmillipore.com)).

## Transformation and Amplification of Plasmid

DH5α, DH10B or equivalent competent cells may be used for the transformation and amplification of the plasmids.

## RNA Synthesis

The complete protocol for RNA synthesis is available in the User Guide for the Simplicon™ Expression System on our website ([www.emdmillipore.com](http://www.emdmillipore.com)).

## Storage & Stability:


**TagGFP2 Simplicon™ Plasmid (E3L):** (CS224504) One (1) vial containing 10 µL of DNA (1 µg/µL). Store at -20 °C.

## References

1. Petrakova O, et al. 2005 *J Virol* **79**(12): 7597-7608.
2. Zimmer G 2010 *Viruses* **2**(2): 413-434.
3. Yoshioka N, et al. 2013 *Cell Stem Cell*. **13** (2): 246-254.
4. Yoshioka N, et al. 2017 *PLoS One*. **12**(7): e0182018.
5. Perdiguer B, et al. 2009 *J Interferon Cytokine Res*. **29**(9): 581-98.
6. Pegg G, et al. 2018 *Drug Metabolism and Pharmacokinetics* **33** (1): S33-S34.
7. Mertzlyak EM, et al. 2007 *Nat. Methods* **4**: 555-557.
8. Subach OM, et al. 2008 *Chem. Biol.* **15**: 1116-1124.

Please visit [www.millipore.com](http://www.millipore.com) for additional product information and references.

Submit your published journal article, and earn credit toward future purchases. Visit [www.millipore.com/publicationrewards](http://www.millipore.com/publicationrewards) to learn more!



**T7 promoter:** Partial promoter for bacteriophage T7 RNA polymerase. Allows *in vitro* transcription of the Simplicon™ RNA.

**Non-structural genes (nsP1-4):** Encodes four nonstructural proteins (nsP1-4) that are responsible for replication of Simplicon™ RNA (genomic RNA) and transcription of subgenomic RNA (your genes, E3L and puromycin).

**26S Subgenomic Promoter:** Promotes the transcription of subgenomic RNAs with nsP proteins.

**TagGFP2:** Encodes TagGFP2 gene.

**IRES:** Internal Ribosome Entry Site. Allows for translation of E3L and Puromycin genes.

**E3L:** Encodes Vaccinia virus E3L gene. Human codon optimized.

**PuroR:** Encodes puromycin resistance gene. Confers resistance to puromycin.

**3' UTR:** Partial 3' UTR from VEE RNA replicon.

**Poly (A):** Long poly (A) tail (175 nucleotides) is incorporated into the vector and thus the poly (A) adenylation reaction is no longer required.

**AmpR:** Ampicillin resistance gene. Confers resistance to ampicillin in *E. coli*.

**Ori:** high-copy-number ColE1/pMB1/pBR322/pUC origin of replication in *E. coli*.

Full DNA sequences are available from our website: [www.emdmillipore.com](http://www.emdmillipore.com)

■ antibodies ■ Multiplex products ■ biotools ■ cell culture ■ enzymes ■ kits ■ proteins/peptides ■ siRNA/cDNA products

Please visit [www.millipore.com](http://www.millipore.com) for additional product information, test data and references

EMD Millipore Corporation, 28820 Single Oak Drive, Temecula, CA 92590, USA 1-800-437-7500

Technical Support: T: 1-800-MILLIPORE (1-800-645-5476) • F: 1-800-437-7502

FOR RESEARCH USE ONLY. Not for use in diagnostic procedures. Not for human or animal consumption. Purchase of this Product does not include any right to resell or transfer, either as a stand-alone product or as a component of another product. Any use of this Product for purposes other than research is strictly prohibited.

EMD Millipore®, the M mark, Upstate®, Chemicon®, Linco® and all other registered trademarks, unless specifically identified above in the text as belonging to a third party, are owned by Merck KGaA, Darmstadt, Germany. Copyright ©2008-2018 Merck KGaA, Darmstadt, Germany. All rights reserved.



We Buy 100% Certified Renewable Energy

## RELATED PRODUCTS

| Cat #  | Description   |
|--------|---|
| SCR720 | ■ TagGFP2 Simplicon™ RNA (E3L) Kit                        |
| SCR721 | ■ TagRFP Simplicon™ RNA (E3L) Kit                         |
| SCR722 | B18R-E3L RNA (human codon optimized for B18R and E3L)     |
| SCR723 | B18R RNA (human codon optimized)                          |
| SCR724 | Simplicon™ Cloning Vector (E3L)                           |
| SCR726 | TagRFP Simplicon™ Plasmid (E3L)                           |
| SCR727 | B18R-E3L Plasmid (human codon optimized for B18R and E3L) |
| SCR728 | B18R Plasmid (human codon optimized)                      |
| SCR729 | Human OKSG-cMyc TagRFP Simplicon™ Plasmid                 |
| GF156  | B18R protein (produced from insect)                       |
| GF197  | B18R protein (produced from HEK 293 cells)                |

### RESTRICTED USE AGREEMENT (subject to local law)

**THIS PRODUCT MAY ONLY BE USED FOR RESEARCH PURPOSES, WHICH IS FURTHER DEFINED BELOW. BY OPENING THIS PRODUCT, YOU (“PURCHASER”) HEREBY REPRESENT THAT YOU HAVE THE RIGHT AND AUTHORITY TO LEGALLY BIND YOURSELF AND/OR YOUR EMPLOYER, AS APPLICABLE, AND CONSENT TO BE LEGALLY BOUND BY THE TERMS OF THIS RESTRICTED USE AGREEMENT. IF YOU DO NOT AGREE TO COMPLY WITH THESE TERMS, YOU MAY NOT OPEN OR USE THE PRODUCT AND YOU MUST CALL MILLIPORESIGMA (“SELLER”) CUSTOMER SERVICE (1-800-645-5476) TO ARRANGE TO RETURN THE PRODUCT FOR A REFUND.**

“Product” means TagGFP2 Simplicon™ Plasmid (E3L) (SCR725)

“Research Purposes” means any internal *in vitro* research use and specifically excludes the following uses of whatever kind or nature:

- Re-engineering or copying the Product
- Making derivatives, modifications, or functional equivalents of the Product
- Obtaining patents or other intellectual property rights claiming use of the Product
- Using the Product in the development, testing, or manufacture of a Commercial Product
- Using the Product as a component of a Commercial Product
- Reselling or licensing the Product
- Using the Product in clinical or therapeutic applications including producing materials for clinical trials
- Administering the Product to humans
- Using the Product in collaboration with a commercial or non-academic entity

“Commercial Product” means any product intended for: (i) current or future sale; (ii) use in a fee-for-service; or (iii) any diagnostic, clinical, or therapeutic use.

Access to the Product is limited solely to PURCHASER’s officers, employees, and students who need to use the Product for Research Purposes. PURCHASER shall comply with all applicable laws in its use and handling of the Product and shall keep it under reasonably safe and secure conditions to prevent unauthorized use or access.

These restrictions will remain in effect for as long as PURCHASER possesses the Product.

**PLEASE CONTACT [licensing@emdmillipore.com](mailto:licensing@emdmillipore.com) PRIOR TO PURCHASE FOR ANY USE OF THE PRODUCT OUTSIDE OF THIS RESTRICTED USE AGREEMENT.**

■ antibodies ■ Multiplex products ■ biotools ■ cell culture ■ enzymes ■ kits ■ proteins/peptides ■ siRNA/cDNA products

Please visit [www.millipore.com](http://www.millipore.com) for additional product information, test data and references

EMD Millipore Corporation, 28820 Single Oak Drive, Temecula, CA 92590, USA 1-800-437-7500

Technical Support: T: 1-800-MILLIPORE (1-800-645-5476) • F: 1-800-437-7502

FOR RESEARCH USE ONLY. Not for use in diagnostic procedures. Not for human or animal consumption. Purchase of this Product does not include any right to resell or transfer, either as a stand-alone product or as a component of another product. Any use of this Product for purposes other than research is strictly prohibited.

EMD Millipore®, the M mark, Upstate®, Chemicon®, Linco® and all other registered trademarks, unless specifically identified above in the text as belonging to a third party, are owned by Merck KGaA, Darmstadt, Germany. Copyright ©2008-2018 Merck KGaA, Darmstadt, Germany. All rights reserved.



We Buy 100% Certified Renewable Energy