


# **Restriction Endonuclease Stu I**

From Streptomyces nodosus

Cat. No. 10 753 351 001 Cat. No. 11 047 680 001

500 units (10 U/ $\mu$ l) 2500 units, high concentration (40 U/ $\mu$ l)



☐ Version 17 Content version: February 2012

Store at -15 to -25°C

Stability/Storage

The undiluted enzyme solution is stable when stored at -15 to  $-25^{\circ}\text{C}$  until the control date printed on the label. Do not store below -25°C to avoid freezing.

Sequence specificity

*Stu* I recognizes the sequence AGG/CCT and generates fragments with blunt ends (1).

Compatible ends

Stu I is compatible to any blunt end.

Isoschizomers

The enzyme is an isoschizomer to Aat I and Eco 147I.

Methylation sensitivity

Stu I is inhibited at AGG/\*C\*CT by the presence of 5'-methylcytosine, as indicated (\*).

Storage buffer

20 mM Tris-HCl, 100 mM NaCl, 0.1 mM EDTA, 10 mM 2-Mercaptoethanol, 0.05% Triton X-100 (v/v), 50% Glycerol (v/v), pH approx. 7.9 (at 4°C).

Incubation buffer 10 x

100 mM Tris-HCl, 1 M NaCl, 50 mM MgCl $_2$ , 10 mM 2-Mercaptoethanol, pH 8.0 (at 37°C), ( $\triangleq$  SuRE/Cut buffer B).

Activity in SuRE/Cut Buffer System

Bold face printed buffer indicates the recommended buffer for optimal activity:

Α	В	L	M	Н
100%	100%	100%	50-75%	50-75%

# Incubation temperature

3**7°C** 

**Unit definition** 

One unit is the enzyme activity that completely cleaves 1  $\mu$ g  $\lambda$ DNA in 1 h at  $37^{\circ}C$  in SuRE/Cut buffer **B** in a total volume of 25  $\mu$ l.

### Typical experiment

Component	Final concentration	
DNA	1 μg / 25 μl	
10 × SuRE/Cut Buffer <b>B</b>	2.5 µl	
Sterile repurified water	Up to a total volume of 25 μl	
Restriction enzyme	1 unit	

Incubate at 37°C for 1 h.

#### Heat inactivation

The enzyme can be heat inactivated by heating to  $65^{\circ}$ C for 15 min.

### Number of cleavage sites on different DNAs (2):

λ	Ad2	SV40	Φ X174	M13mp7	pBR322	pBR328	pUC18
6	11	7	1	0	0	0	0

### Activity in PCR buffer

Relative activity in PCR mix (Taq DNA Polymerase buffer) is 30%. The PCR mix contained  $\lambda$  target DNA, primers, 10 mM Tris-HCl (pH 8.3, 20°C), 50 mM KCl, 1.5 mM MgCl $_2$ , 200  $\mu$ M dNTPs, 2.5 U Taq DNA polymerase. The mix was subjected to 25 amplification cycles.

# Ligation and recutting assay

Stu I fragments obtained by complete digestion of 1 μg λDNA are ligated with 1 U T4-DNA ligase (Cat. No. 10 481 220 001) in a volume of 10 μl by incubation for 16 h at 25°C in 66 mM Tris-HCl, 5 mM MgCl<sub>2</sub>, 5 mM Dithiothreitol, 1 mM ATP, pH 7.5 (at 20°C) resulting in > 90 % recovery of 1 μg λDNA fragments. Subsequent re-cutting with Stu I yields > 95% of the typical pattern of λDNA × Stu I fragments.

#### **Troubleshooting**

A critical component is the DNA substrate. Many compounds used in the isolation of DNA such as phenol, chloroform, ethanol, SDS, high levels of NaCl, metal ions (e.g., Hg²+, Mn²+) inhibit or alter recognition specificity of many restriction enzymes. Such compounds should be removed by ethanol precipitation followed by drying, before the DNA is added to the restriction digest reaction. Appropriate mixing of the enzyme is recommended.

#### **Quality control**

Lot-specific certificates of analysis are available at www.roche-applied-science.com/certificates.

Absence of unspecific endonuclease activities

Absence of exonuclease activity

fer B with excess of *Stu* I. The number of enzyme units which do not change the enzyme-specific pattern is stated in the certificate of analysis.

Approx. 5 µg [<sup>3</sup>H] labeled calf thymus DNA are incubated with 3 µl Stu I for 4 h at 37°C in a total volume of 100 µl

1  $\mu g$   $\lambda DNA$  is incubated for 16 h in 50  $\mu l$  SuRE/Cut buf-

Approx. 5  $\mu$ g [ $^3$ H] labeled calf thymus DNA are incubated with 3  $\mu$ l Stul for 4 h at 37°C in a total volume of 100  $\mu$ l 50 mM Tris-HCl, 10 mM MgCl<sub>2</sub>, 1 mM Dithioerythritol, pH approx. 7.5. Under these conditions, no release of radioactivity is detectable, as stated in the certificate of analysis).

#### References

- 1 Shimotsu, H. et al. (1980) Gene **11**, 219.
- Kessler, C. & Manta V. (1990) Gene 92, 1–248
   Bolivar, F. and Backman, K. (1980) in: Methods in Enzymology
- 3 Bolivar, F. and Backman, K. (1980) in: Methods in Enzymology (Colowick, S.P. and Kaplan, N.O., eds.) Acad. Press New York 68, 245.
- 4 McDonell, M.W. et al. (1977) J. Mol. Biol. **110,** 119.
- 5 Roberts, R.J. (1983) Nucl. Acids Res. **11**, 135.
- Sanger, F. et al. (1982) J. Mol. Biol. **162**, 729. Schaffner, W. et al. (1976) Cell **8**, 471.
- 8 Shinnick, T.M. (1975) Nucl. Acids Res. 2, 1911.
- 9 Rebase The Restriction Enzyme Database: http://rebase.neb.com
- 10 Benchmate: http://roche-applied-science.com/benchmate

#### **Ordering Information**

Roche Applied Science offers a large selection of reagents and systems for life science research. For a complete overview of related products and manuals, please visit and bookmark our home page, <a href="https://www.roche-applied-science.com">www.roche-applied-science.com</a>, and our Special Interest Sites, including "Mapping & Cloning": <a href="http://www.restriction-enzymes.com">http://www.restriction-enzymes.com</a>.

The convenient RE Finder Program located on our Bench Mate website, <a href="http://www.roche-applied-science.com/benchmate">http://www.roche-applied-science.com/benchmate</a> helps you identify the enzymes that will cut your DNA sequence, and displays the names and recognition sequences of enzymes and isoschizomers as well as links to detailed information (e.g. instructions for use) of the selected restriction enzyme.

Product	Application	Packsize	Cat. No.
Restriction Enzymes	DNA restriction digestion	Please refer to websit	e or catalogue
Rapid DNA Liga- tion Kit	Ligation of sticky- or blunt-ended DNA fragments in just 5 min at +15 to +25 °C.	Kit (40 DNA ligations)	11 635 379 001
T4 DNA Ligase	Ligation of sticky- and blunt- ended DNA fragments.	100 U 500 units (1 U/μl)	10 481 220 001 10 716 359 001
rAPid Phosphatase	Dephosphorylation of 5´-phosphate residues from nucleic acids	1000 U 5000 U	04 898 133 001 04 898 141 001
rAPid Dephos and Ligation Kit	Dephosphorylation of nucleic acids.	40 reactions 160 reactions	04 898 117 001 04 898 125 001
Alkaline Phospha- tase (AP), special quality for molecu- lar biology	Dephosphorylation of 5'-phosphate residues from nucleic acids.	1000 U (20 U/µl)	11 097 075 001
Agarose MP	Multipurpose agarose for analytical and prepara- tive electrophoresis of nucleic acids	100 g 500 g	11 388 983 001 11 388 991 001
Agarose LE	Separation of nucleic acids in the range 0.2 - 1.5 kbp	100 g 500 g	11 685 660 001 11 685 678 001
Agarose Gel DNA Extraction Kit	For the elution of DNA fragments from agarose gels.	1 Kit (max. 100 reactions)	11 696 505 001
High Pure PCR Product Purifica- tion Kit	Purification of PCR or enzymatic modification reaction (e.g. restriction digest)	50 purifications 250 purifications	11 732 668 001 11 732 676 001
SuRE/Cut Buffer Set for Restriction Enzymes	Incubation buffers A, B, L, M and H for restriction enzymes	1 ml each (10× conc. solutions)	11 082 035 001
SuRE/Cut Buffer A	Restriction enzyme incubation	5 × 1 ml (10× conc. solution)	11 417 959 001
SuRE/Cut Buffer B	Restriction enzyme incubation	5 × 1 ml (10× conc. solution)	11 417 967 001
SuRE/Cut Buffer H	Restriction enzyme incubation	5 × 1 ml (10× conc. solution)	11 417 991 001
SuRE/Cut Buffer L	Restriction enzyme incubation	5 × 1 ml (10× conc. solution)	11 417 975 001
SuRE/Cut Buffer M	Restriction enzyme incubation	5 × 1 ml (10× conc. solution)	11 417 983 001
Water, PCR Grade	Specially purified, double-distilled,	100 ml (4 vials of 25 ml)	03 315 843 001
	deionized, and autoclaved	25 ml (25 vials of 1 ml) 25 ml	03 315 932 001 03 315 959 001
		(1 vial of 25 ml)	
BSA, special qual- ity for molecular biology	Maintaining enzyme stability	20 mg (1 ml)	10 711 454 001

#### **Printed Materials**

You can view the following manuals on our website

You can view the following manuals on our website.
Lab FAQS "Find a Quick Solution"
Restriction Enzyme Ordering Guide
Molecular Weight Markers for Nucleic Acids

### Changes to previous version

Update of quality control.

#### Trademarks

HIGH PURE and SURE/CUT are trademarks of Roche. All other product names and trademarks are the property of their respective owners.

#### Regulatory Disclaimer

For life science research only. Not for use in diagnostic procedures.

#### **Commonly used bacterial strains**

Strain	Genotype
BL21	E. coli B $F^-$ dcm ompT hsdS( $r_B^ m_B^-$ ) gal (Studier, F.W. et al (1986) J. Mol. Biol., <b>189</b> , 113.)
C600 <sup>e</sup>	supE44 hsdR2 thi-1 thr-1 leuB6 lacY1 tonA21; (Hanahan, D. (1983) J. Mol. Biol. <b>166</b> , 557.)
DH5α	supE44 Δ(lacU169 (φ80dlacZΔM15) hsdR17 recA1 endA1 gyrA96 thi-1 relA1; (Hanahan, D. (1983) J. Mol. Biol. <b>166</b> , 557.)
HB101	supE44 hsdS20 recA13 ara-14 proA2 lacY1 galK2 rpsL20 xyl-5 mtl-1; (Hanahan, D., (1983) J. Mol. Biol. <b>166</b> , 557.)
JM108	recA1 supE44 endA1 hsdR17 gyrA96 relA1 thi $\Delta$ (lac-proAB); (Yanisch- Perron, C. et al., (1985) Gene <b>33</b> , 103.)
JM109	recA1 supE44 endA1 hsdR17 gyrA96 relA1 thi $\Delta$ (lac-proAB) F[traD36proAB $^+$ , lacl $^q$ lacZ $\Delta$ M15]; (Yanisch- Perron, C. et al., (1985) Gene <b>33</b> , 103.)
JM110	rpsL (Str <sup>l</sup> ) thr leu thi-l lacY galK galT ara tonA tsx dam dcm supE44 Δ(lac-proAB) F'[traD36proAB <sup>+</sup> , lacl <sup>q</sup> lacZΔM15]; (Yanisch- Perron, C. et al., (1985) Gene <b>33</b> , 103.)
K802	supE hsdR gal metB; (Raleigh, E. et al., (1986) Proc.Natl. Acad.Sci USA, 83, 9070.; Wood, W.B. (1966) J. Mol. Biol., <b>16</b> , 118.)
SURE <sup>r</sup>	recB recJ sbc C201 uvrC umuC::Tn5(kan') lac , Δ(hsdRMS) endA1 gyrA96 thi relA1 supE44 F'[proAB <sup>+</sup> lacl <sup>q</sup> lacZΔM15 Tn10 (tet'); (Greener, A. (1990) Stratagies, <b>3</b> , 5.)
TG1	supE hsd Δ5 thi Δ(lac-proAB) F'[traD36proAB <sup>+</sup> , lacl <sup>q</sup> lacZΔM15]; (Gibson, T.J. (1984) PhD Theses. Cambridge University, U.K.)
XL1-Blue <sup>r</sup>	supE44 hsdR17 recA1 endA1 gyrA46 thi relA1 lac F'[proAB $^+$ , lacl $^q$ lacZ $\Delta$ M15 Tn10 (tet $^D$ ]; (Bullock et al., (1987) BioTechniques, 5, 376.)

#### **Contact and Support**

To ask questions, solve problems, suggest enhancements or report new applications, please visit our **Online Technical Support Site** at:

### www.roche-applied-science.com/support

To call, write, fax, or email us, visit the Roche Applied Science home page, www.roche-applied-science.com, and select your home country. Country-specific contact information will be displayed. Use the Product Search function to find Pack Inserts and Material Safety Data Sheets.

