

Product Information

Doxorubicin, Ready-Made

2 mg/mL Suitable for cell culture

D5220

Product Description

Doxorubicin (DOX) is an anthracycline antibiotic isolated from *Streptomyces peucetius var. caesius*. A hydroxy derivative of daunorubicin, DOX is naturally fluorescent anthracycline antibiotic and an anticancer drug.

This readymade solution contains doxorubicin hydrochloride at a concentration of 2 mg/mL in DMSO.

Precautions and Disclaimer

For R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

Storage/Stability

Store this product at -20 °C. At the indicated temperature, the product is stable for at least 2 years.

Activity

Doxorubicin inhibits topoisomerase II¹ by intercalating between base pairs and by inducing strand breaks, resulting in the inhibition of nucleic acid and protein synthesis. It also contributes to the formation of free radicals for the disruption of membrane lipids and DNA strands. It is used in the treatment of non-Hodgkin's lymphoma and other cancers. DOX is a substrate of MRP1; used for measurement of drug efflux pump activities and for identification of MRP1 inhibitors².

References

1. Int J Mol Sci. 2018 19(11): 3480. doi: 10.3390/ijms19113480.
2. Biomed Pharmacother. 2019 **118**:109289. doi: 10.1016/j.biopha.2019.109289.

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the U.S. and Canada.

MilliporeSigma, and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.
© 2022 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.

D5220pis Rev 0922

Notice

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

The information in this document is subject to change without notice and should not be construed as a commitment by the manufacturing or selling entity, or an affiliate. We assume no responsibility for any errors that may appear in this document.

Technical Assistance

Visit the tech service page at SigmaAldrich.com/techservice.

Terms and Conditions of Sale

Warranty, use restrictions, and other conditions of sale may be found at SigmaAldrich.com/terms.

Contact Information

For the location of the office nearest you, go to SigmaAldrich.com/offices.