

Manganese Superoxide Dismutase (MnSOD) and Histone H2A.X Phosphorylation Assay

For High Content Screening

For 5 x 96-well plates

Cat. No. HCS233

FOR RESEARCH USE ONLY Not for use in diagnostic procedures.

USA & Canada Phone: +1(800) 437-7500 Fax: +1 (951) 676-9209 Australia +61 3 9839 2000 www.millipore.com

Introduction

(i) High Content Screening

High Content Screening (HCS) technology offers a major opportunity to improve the drug discovery and development process [1]. HCS enables the evaluation of multiple biochemical and morphological parameters in cellular systems and facilitates characterization of the subcellular distribution of fluorescent signals with labeled reagents. By combining automated imaging of cells with validated detection reagents and powerful image analysis algorithms, scientists can now acquire deeper knowledge of multiple pathways at the single-cell level, usually in a single assay, at an early stage in the development of new drugs [2]. HCS platforms such as the IN Cell Analyzer (GE Healthcare), ArrayScan (ThermoFisher Scientific), or Opera (Perkin Elmer), can be used to deliver detailed profiles of cellular responses [3].

Successful HCS assays rely on high quality reagents [4]. With the commercial availability of thousands of immunoreagents and fluorescent probes, large numbers of fixed-endpoint HCS assays are possible. However, incompatibility of reagents when integrated into a single assay can lead to a significant drop-off in assay performance. Immunoreagents for HCS assays carry special requirements. Strong antigen affinity is required, minimal non-specific binding must be observed, interactions between multiple primary or secondary immunoreagents must be minimized, and the signal to background ratio must be sufficient to ensure an adequate screening window [4]. Additionally, to enable scale up of HCS assays, the sample preparation protocol must be highly reproducible, and the reagents must exhibit minimal assay-to-assay variability.

(ii) Manganese superoxide dismutase (MnSOD), Histone H2A.X phosphorylation and their significance in cell biology and drug discovery

Manganese superoxide dismutase (MnSOD)

Reactive oxygen species (ROS), such as superoxide anion radicals and hydrogen peroxide, are potentially harmful by-products of normal cellular metabolism [5]. ROS normally exist in the cell in balance with antioxidant molecules. Oxidative stress occurs when this balance is disrupted due to depletion of antioxidants or excess accumulation of ROS, or both [6]. Many inducers of oxidative stress are known carcinogens, mutagens, and toxins. Accordingly, oxidative stress is a common denominator in many diseases and environmental insults and can lead to severe cellular damage leading to physiological dysfunction and cell death. When oxidative stress occurs, cells function to restore redox balance by resetting critical homeostatic parameters. One rapid and clear indicator of oxidative stress is the induction of antioxidant defenses [6].

To minimize the damaging effects of ROS, cells utilize an array of defenses. Enzymatic defenses, such as superoxide dismutases (SOD) and catalases (CAT), protect by scavenging superoxide radicals and hydrogen peroxide respectively, converting them to less reactive species. SOD guard against superoxide toxicity, protecting redox-sensitive cellular machinery from damage by catalyzing the disproportionation of superoxide anion to oxygen and hydrogen peroxide. Thus, the SOD and CAT serve, in tandem, as front-line antioxidant defenses [6].

The manganese-containing superoxide dismutase of the mitochondria (MnSOD) plays an essential role in oxidative stress protection [7], and has been shown by knockout mice studies to be essential for life [8]. MnSOD is an inducible antioxidant enzyme protecting mitochondria from oxidative damage [9]. Numerous studies have shown that MnSOD can be induced to protect against prooxidant insults resulting from cytokine treatment, ultraviolet light, irradiation, certain tumors, amyotrophic lateral sclerosis, and ischemia/ reperfusion [8]. Thus, it is important to know the status

of both MnSOD protein levels and activity in order to assess its role as an important regulator of cell biology [8].

Mitochondrial reactive oxygen species (ROS) represent a target for drug discovery since their production is characteristic of early stages of apoptosis [10]. In fact, many antitumor agents, such as vinblastine, cisplatin, doxorubicin, camptothecin and many others exhibit antitumor activity via ROSdependent activation of apoptotic cell death [5]. Since MnSOD expression is upregulated in response to ROS, quantitation of MnSOD expression represents a useful drug screening tool.

Several lines of evidence suggest the possibility of MnSOD as a target for new, effective and possibly tumor-selective anticancer treatments [9]. Elevated levels of MnSOD are found in several classes of human neoplasms, in a fashion which often correlates with the degree of their malignancy. Recent observations suggest that pharmacological inhibition of MnSOD may represent an effective strategy to selectively kill cancer cells and to circumvent their resistance to commonly used anticancer treatments [9]. Thus, MnSOD may serve a dual role in health and disease, in that oxidants should be eliminated by MnSOD in normal cells, but may prove useful once a tumor has developed, to promote the chemosensitivity of cancer cells [9].

Histone H2A.X Phosphorylation

Many key scientific discoveries have been made that link specific histone modifications with important biological phenomena. In particular, histone modifications have been discovered that are useful biomarkers of genotoxic DNA damage and apoptosis. One of the principal responses to DNA damage resulting in double-stranded DNA breaks (DSBs) is the activation of the ATM-initiated signaling cascade to arrest cell division until repairs can be made [11]. Agents that cause DNA damage and DSBs include oxidative stress, ionizing radiation, topoisomerase inhibitors, and DNA binding drugs [12, 13]. A major substrate of the kinases in this cascade is H2A.X. H2A.X is a variant isoform of the histone H2A protein, containing several serine residues (including serine 139) in its unique carboxy-terminal amino acid sequence that are rapidly phosphorylated in response to DSBs [14, 15]. H2A.X is rapidly phosphorylated at serine 139 by the ATM kinase in response to even a few DSBs, and accumulates at the sites of DNA damage forming distinct nuclear foci [16]. These events are important for recruitment and maintenance of DNA repair machinery, including p53, to the site of the break [11, 16]. Thus the presence of phospho-histone H2A.X ^(Ser139) foci is a reliable marker of DSBs and DNA damage. As DNA repair progresses, the number of foci declines. Genotoxic events resulting from reactive oxygen species (ROS) and oxidative stress in a wide variety of cell types result in phosphorylation of H2A.X at serine 139 [17-23], thus phospho-histone H2A.X (Ser139) also serves as a useful downstream marker of oxidative damage.

When the DNA damage is severe, the cell will undergo apoptosis, which involves processing of the genome into small fragments and creating more DSBs [15]. Consequently, H2A.X phosphorylated at serine 139 (sometimes referred to as γH2A.X) can also be used as a marker for apoptosis. Since this modification occurs very early in the apoptotic pathway, long before many characteristic morphological changes are detectable, it is one of the earliest indicators of apoptosis.

Detection and quantification of phospho-histone H2A. $X^{(Ser139)}$ foci as an indicator of oxidative stress, DNA damage, repair and apoptosis is of great interest to researchers investigating these pathways [17-24]. Additionally, recent data indicates that phospho-histone H2A.X^(Ser139) may have additional cellular functions which have yet to be fully elucidated, representing a focus of ongoing research [25]. High Content Screening technology represents an ideal tool for performing quantitative analysis of phospho-histone H2A.X (Ser139) expression. This has been recently demonstrated by the work of Das *et al*. [26], who performed HCS analysis of γH2A.X foci to analyze potential therapeutic approaches for non-small cell lung cancers.

Application

Millipore's HCS233 assay provides a complete solution for identifying and quantifying manganese superoxide dismutase (MnSOD) and phospho-histone H2A.X^(Ser139) in cellular imaging studies. The reagents in the kit have been specifically optimized for HCS applications.

The assay is designed to enable visualization and quantitative detection of MnSOD and phosphorylated histone H2A.X, allowing the characterization of the oxidative stress response, genotoxicity, and screening of compounds that may induce, inhibit or repair cellular injury such as DNA damage, oxidative stress and inflammation. The nuclear dye (Hoechst 33342) may be used for measurements of cell number, DNA content and nuclear size. Additionally, the assay can be multiplexed with other probes, *e.g.*, for apoptotic pathway studies, oncology drug efficacy trials or *in vitro* toxicology applications.

The assay is immunofluorescence-based, and utilizes a rabbit polyclonal antibody which identifies MnSOD in human, mouse, rat and bovine cells (not canine). Alternate species cross-reactivity must be confirmed by the end user. The assay also uses a high quality mouse monoclonal antibody which identifies phospho-histone H2A.X $(SET 139)$ in human cells. Broad species cross-reactivity is expected, but must be confirmed by the end user. The superior Millipore reagents provided with this kit enable the user to reproducibly generate images with a high signal-to-background ratio, greatly facilitating HCS. In addition, working solutions of the primary and secondary antibodies are stable for at least 24 hours at room temperature (Figure 4), a great benefit for large-scale screening applications. The straightforward sample preparation and processing protocol takes less than 2.5 hrs after fixation.

Reagents are provided for 5 x 96-well microplates – *i.e.*, sufficient to perform 480 separate experiments. The kit includes a rabbit primary antibody for manganese superoxide dismutase, a mouse primary antibody for phospho-histone H2A.X^{'(Ser139)}, a Cy3-conjugated anti-rabbit IgG secondary antibody, a FITC-conjugated anti-mouse IgG secondary antibody, Hoechst HCS Nuclear Stain, HCS Fixation Solution, HCS Immunofluorescence Buffer, HCS Wash Buffer, and Plate Sealers. Two DNA Damage control compounds, the chemotherapeutic drugs camptothecin and etoposide, along with DMSO for Compound Serial Dilution and Compound Dilution Buffer, are also included in the kit, sufficient for duplicate 12-point dose response samples per plate (see Assay Instructions). Camptothecin, a DNA topoisomerase I inhibitor, and etoposide, a DNA topoisomerase II inhibitor [27, 28], have both been shown to induce ROS, to interfere with DNA replication/synthesis, and to induce double-strand DNA breaks.

For Research Use Only; Not for use in diagnostic procedures

Kit Components

- 1. Rabbit Anti-Manganese Superoxide Dismutase (MnSOD) HCS Primary Antibody, 100X: (Part No. CS201736) 1 vial containing 300 µL.
- 2. HCS Secondary Antibody (donkey anti-rabbit IgG, Cy3 conjugate), 200X: (Part No. CS201659) 1 vial containing 150 µL.
- 3. Mouse Anti-Phospho-Histone H2A.X^(Ser139) HCS Primary Antibody, 100X: (Part No. CS201685) 1 vial containing 300 µL.
- 4. HCS Secondary Antibody (donkey anti-mouse IgG, FITC conjugate), 200X: (Part No. CS201651) 1 vial containing 150 µL.
- 5. Hoechst HCS Nuclear Stain, 200X: (Part No. CS200438) 1 vial containing 150 µL.
- 6. HCS Fixation Solution with Phenol Red, 2X: (Part No. CS200434) 1 bottle containing 100 mL.
- 7. HCS Immunofluorescence Buffer, 1X: (Part No. CS200435) 1 bottle containing 1000 mL.
- 8. HCS Wash Buffer, 1X: (Part No. 2007643) 1 bottle containing 500 mL.
- 9. Camptothecin, 2.5mM in DMSO, 250X: (Part No. CS201666) 1 vial containing 100 µL.
- 10. Etoposide, 25mM in DMSO, 250X: (Part No. CS200439) 1 vial containing 100 µL.
- 11. DMSO for Compound Serial Dilution: (Part No. CS200441) 1 bottle containing 10 mL.
- 12. Compound Dilution Buffer: (Part No. CS200442) 1 bottle containing 25 mL.
- 13. Plate Sealers: (Part No. CS200443) 10 each.

Materials Not Supplied

- 1. Sterile, tissue culture-treated black/clear bottom microplates suitable for High-Content Imaging.
- 2. Cell-type for assay, *e.g.*, HeLa (human cervical adenocarcinoma, ATCC #CCL-2), A549 (human lung carcinoma, ATCC #CCL-185) or HepG2 (human hepatocellular carcinoma, ATCC #HB-8065).
- 3. Tissue culture instruments/supplies (including 37ºC incubator, growth media, flasks/plates, detachment buffer, etc.) for cell type of interest.
- 4. HCS imaging/analysis system, *e.g.*, GE Healthcare IN Cell Analyzer 1000 with Investigator software. System must be equipped with beam-splitters and filters capable of reading emission spectra in the blue and red ranges. Detailed image acquisition and analysis guidelines are provided in Table 2.

Precautions

1. This product contains hazardous materials. Refer to MSDS for further information.

2. For Research Use Only. Not for use in diagnostic procedures.

Storage

Store kit components under the conditions indicated on the labels. HCS Fixation Solution, HCS Immunofluorescence Buffer, HCS Wash Buffer, DMSO, and Compound Dilution Buffer should be stored at 2-8ºC. Plate Sealers may be stored at room temperature. HCS Primary Antibodies, HCS Secondary Antibodies, Hoechst HCS Nuclear Stain, Camptothecin and Etoposide should be stored at -20ºC, avoiding repeated freeze/thaw cycles. Discard any remaining reagents after 6 months.

(Note: If kit is expected to be used for multiple experiments, rather than a single use, thaw antibodies, nuclear stain and control compounds and dispense into appropriately sized aliquots. Store aliquots at -20ºC.)

Assay Instructions

Note: The HCS233 assay protocol has been optimized for HeLa human cervical carcinoma (ATCC #CCL-2), A549 human lung carcinoma (ATCC #CCL-185) and HepG2 human hepatocellular carcinoma (ATCC #HB-8065) cells. However, this kit is suitable for HCS analysis of a variety of human cell types. Alternate species reactivity must be confirmed by the end user.

Cell Preparation:

- 1. Prior to cell seeding for assay, culture HeLa, A549 or HepG2 cells in growth media until ~70-80% confluent.
- 2. Detach cells from culture flasks/plates via method appropriate for cell type of interest. If necessary, coat assay plate wells with extracellular matrix protein (*e.g.*, collagen I for HepG2) to enhance cell adhesion. Adjust cell density to 5-7 x 10⁴ cells/mL (Hela/A549) or 1-2 x 10⁵ cells/mL (HepG2) in growth media. Add 90 µL of this cell suspension to each well (for a 96-well plate, this is approximately equivalent to 15,000-21,000 HeLa or A549 cells/cm² of well surface, or 30,000-60,000 HepG2 cells/cm²). After adding cells to plate, allow plate to sit on a level surface at room temperature for 15-30 min, which allows for even cell distribution. Following this period, incubate cells in growth media (37 \textdegree C/5% CO₂) for \textdegree 24-48 hours.
- 3. Cell treatments (control compounds, test compounds, etc.) can be introduced at any point during this culture period, as appropriate for time-course of treatment of interest. Camptothecin and Etoposide are provided as DNA Damage control compounds. Sufficient reagents are provided for duplicate 12-point dose response curves (including one DMSO-control set within the dose response) for all five 96-well plates. The compounds are provided at 250X concentration (assuming maximum treatments of 10 µM and 100 µM for camptothecin and etoposide, respectively). Recommended treatment preparation involves half-log (1:√10) serial dilution of the 250X compound in DMSO, followed by dilution in Compound Dilution Buffer to 10X. 10 µL of each treatment may then be added to the 90 μ L of culture media already present in each well, for a final 1X concentration (0.4% DMSO). Sample data is provided for 4 or 24hrs of compound treatment at 37°C prior to fixation.

Cell Fixation and Immunofluorescent Staining:

Note: Staining time is ~2.5 hours post-fixation. Do not allow wells to dry out between staining steps. Aspiration and dispensation of reagents should be conducted at low flow rates to diminish any cell loss due to fluid shear. All recommended 'per well' volumes refer to a single well of a 96 well microplate. All recommended 'per 96-well plate' volumes include 25% excess for liquid handling volume loss. All staining steps are performed at room temperature (RT). All buffers and antibody solutions are stable for at least 24 hours at RT (see Figure 3).

- 4. At end of culture period, pre-warm HCS Fixation Solution (2X) to room temperature (RT) or 37ºC if desired (12 mL/96-well plate). In a chemical fume hood, add 100 µL/well directly to culture media and allow to fix for 30 min at RT. Remove fixative/toxin-containing media and dispose of in compliance with regulations for hazardous waste (see MSDS). If proceeding immediately to staining, rinse each well twice with 200 µL of HCS Immunofluorescence Buffer. Alternatively, if plates are to be stained at a later time, rinse twice with 200 µL of Wash Buffer, then leave second rinse volume in wells and store plates tightly sealed at 4ºC until staining.
- 5. If fixed samples have been stored at 4ºC prior to staining, rinse twice with 200 µL HCS Immunofluorescence Buffer before proceeding with staining protocol.
- 6. Prepare working solution of Rabbit Anti-MnSOD/ Mouse Anti-Phospho-Histone H2A.X (Ser139) HCS Primary Antibodies (6 mL/96-well plate) as follows: Add 60 µL of each thawed Primary Antibody to 5.88 mL of HCS Immunofluorescence Buffer (see Table 1). Mix well. Remove previous Immunofluorescence Buffer rinse. Add 50 µL of Primary Antibody solution to each well and incubate for 1 hour at RT.
- 7. Remove Primary Antibody solution. Rinse three times with 200 µL HCS Immunofluorescence Buffer.
- 8. Prepare working solution of Cy3-donkey anti-rabbit IgG/FITC-donkey anti-mouse IgG HCS Secondary Antibodies/Hoechst HCS Nuclear Stain (6 mL/96-well plate) as follows: Add 30 µL of each thawed Secondary Antibody and 30 µL of thawed Hoechst HCS Nuclear Stain to 5.91 mL of HCS Immunofluorescence Buffer (see Table 1). Mix well, protecting solution from light. Remove previous HCS Immunofluorescence Buffer rinse. Add 50 µL of HCS Secondary Antibody/Hoechst HCS Nuclear Stain solution and incubate for 1 hour at RT, protected from light.
- 9. Remove HCS Secondary Antibody/Hoechst HCS Nuclear Stain solution. Rinse twice with 200 µL HCS Immunofluorescence Buffer.
- 10. Remove previous HCS Immunofluorescence Buffer rinse. Rinse twice with 200 µL of HCS Wash Buffer, leaving second rinse volume in wells.
- 11. Seal plate and image immediately, or store plate at 4ºC protected from light until ready for imaging.

Table 1. Detection Reagent Specifications – HCS233 Rabbit Anti-MnSOD / Mouse Anti-Phospho-Histone H2A.X^(Ser139) Assay

Image acquisition and analysis

Table 2. Image Acquisition and Analysis Guidelines – HCS233 Rabbit Anti-MnSOD / Mouse Anti-Phospho-Histone H2A.X^(Ser139) Assay

Sample Results

Figure 1. Immunofluorescence of untreated and toxin-stressed HeLa and HepG2 cells.

HeLa cells were plated at 18,000 cells/cm² (37,000 cells/cm² for HepG2) on 96-well plates in growth media and cultured for 24 hours. Cells were subsequently treated for 24 hours with camptothecin, etoposide or 0.4% DMSO (negative control). Cell handling, fixation and immunostaining were performed according to HCS233 assay protocols. Cells were imaged on the GE IN Cell Analyzer 1000 (3.4) at 20X objective magnification. *Left and center panels*: Monochromatic images of Hoechst HCS Nuclear Stain, phospho-histone H2A.X and MnSOD fluorescence. *Right panel*: Fused images of Hoechst HCS nuclear stain (blue), phospho-histone H2A.X (green) and MnSOD fluorescence (red).

Figure 2. MnSOD dose responses of A549, HeLa and HepG2 cells to toxic stresses.

A549 or HeLa cells were plated at 18,000 cells/cm² (37,000 cells/cm² for HepG2) on 96-well plates in growth media and cultured for 24 hours. Maintaining 48 hours of total culture time, cells were subsequently treated for 4 hours (*left panel*) or 24 hours (*right panel*) with serial dilutions of either camptothecin (max. concentration = 10 μ M) or etoposide (max. concentration = 100 μ M). Cell handling, fixation and immunostaining were performed according to HCS233 assay protocols. Cells were imaged on the GE IN Cell Analyzer 1000 (3.4) at 10X (10 fields/well) and analyzed (nuclear/cytoplasmic segmentation) using the GE IN Cell Analyzer 1000 Workstation (3.5) Multi Target Analysis algorithm. Data presented are mean ± SEM, *n* = 4. Note the minimal MnSOD response after just 4 hours of toxin treatment, compared to the 24 hour time point.

Figure 3. Phospho-histone H2A.X dose responses of A549, HeLa and HepG2 cells to toxic stresses.

A549 or HeLa cells were plated at 18,000 cells/cm² (37,000 cells/cm² for HepG2) on 96-well plates in growth media and cultured for 24 hours. Maintaining 48 hours of total culture time, cells were subsequently treated for 4 hours (*left panel*) or 24 hours (*right panel*) with serial dilutions of either camptothecin (max. concentration = 10 μ M) or etoposide (max. concentration = 100 μ M). Cell handling, fixation and immunostaining were performed according to HCS233 assay protocols. Cells were imaged on the GE IN Cell Analyzer 1000 (3.4) at 10X (10 fields/well) and analyzed (nuclear/cytoplasmic segmentation) using the GE IN Cell Analyzer 1000 Workstation (3.5) Multi Target Analysis algorithm. Data presented are mean ± SEM, *n* = 4. Note the significant phosphohistone H2A.X response after both 4 and 24 hours of toxin treatment.

Figure 4. HCS233 Rabbit Anti-MnSOD / Mouse Anti-Phospho-Histone H2A.X (Ser139) Assay reagent stability.

HeLa cells were seeded at 18,000 cells/cm² on 96-well plates in growth media and cultured for 24 hours, followed by treatment with 0.1 µM camptothecin (CPT) or 0.4% DMSO (negative control) for an additional 24 hours. Samples were fixed and stained under kit conditions, using either fresh buffers and antibody/Hoechst solutions, or buffers and antibody/Hoechst solutions that had been allowed to sit at room temperature (protected from light) for 24 hours prior to staining. Cells were imaged on the GE IN Cell Analyzer 1000 (3.4) at 10X magnification (10 fields/well) and analyzed (nuclear/cytoplasmic segmentation) using the GE IN Cell Analyzer 1000 Workstation (3.5) Multi Target Analysis algorithm. Cytoplasmic signal:background ratios (*i.e.*, Cy3 cytoplasmic:background intensity ratios) were measured to observe MnSOD expression differences between camptothecin and DMSO-treated cells. Nuclear signal:background ratios (*i.e.*, FITC nuclear:cytoplasmic intensity ratios) were measured to observe phospho-histone H2A.X expression differences between camptothecin and DMSO-treated cells. Data presented are mean ± SD; *n* = 3. No significant differences in signal quality were observed between freshly prepared and 24 hour samples.

Troubleshooting

References

- 1. Giuliano KA, Haskins JR, Taylor DL. Advances in high content screening for drug discovery. Assay Drug Dev Technol. 2003;1:565–577. PMID: 15090253
- 2. Giuliano KA, Johnston PA, Gough A, Taylor DL. Systems cell biology based on high-content screening. Methods Enzymol. 2006;414:601-619. PMID: 17110213
- 3. Gough AH, Johnston PA.Requirements, features, and performance of high content screening platforms. Methods Mol Biol. 2007;356:41-61. PMID: 16988394
- 4. Giuliano KA. Optimizing the integration of immunoreagents and fluorescent probes for multiplexed high content screening assays. Methods Mol Biol. 2007;356:189-193. PMID: 16988403
- 5. Fang J, Nakamura H, Iyer AK. Tumor-targeted induction of oxystress for cancer therapy. J Drug Target. 2007;15:475-486. PMID: 17671894
- 6. Scandalios JG. Oxidative stress: molecular perception and transduction of signals triggering antioxidant gene defenses. Braz J Med Biol Res. 2005;38:995-1014. PMID: 16007271
- 7. Culotta VC, Yang M, O'Halloran TV. Activation of superoxide dismutases: putting the metal to the pedal. Biochim Biophys Acta. 2006;1763:747-758. PMID: 16828895
- 8. Macmillan-Crow LA, Cruthirds DL. Invited review: manganese superoxide dismutase in disease. Free Radic Res. 2001;34:325-336. PMID: 11328670
- 9. Pani G, Colavitti R, Bedogni B, Fusco S, Ferraro D, Borrello S, Galeotti T. Mitochondrial superoxide dismutase: a promising target for new anticancer therapies. Curr Med Chem. 2004;11:1299-1308. PMID: 15134521
- 10. Bayir H, Kagan VE. Mitochondrial injury, oxidative stress and apoptosis--there is nothing more practical than a good theory. Crit Care. 2008;12:206-216. PMID: 18341705
- 11. Fernandez-Capetillo O, Chen HT, Celeste A, Ward I, Romanienko PJ, Morales JC, Naka K, Xia Z, Camerini-Otero RD, Motoyama N, Carpenter PB, Bonner WM, Chen J, Nussenzweig A. DNA damage-induced G2-M checkpoint activation by histone H2AX and 53BP1. Nat Cell Biol. 2002;4:993-997. PMID: 12447390
- 12. Crowe SL, Movsesyan VA, Jorgensen TJ, Kondratyev A. Rapid phosphorylation of histone H2A.X following ionotropic glutamate receptor activation. Eur J Neurosci. 2006;23:2351-2361. PMID: 16706843
- 13. Li Z, Yang J, Huang H. Oxidative stress induces H2AX phosphorylation in human spermatozoa. FEBS Lett. 2006;580:6161-6168. PMID: 17064697
- 14. Rogakou EP, Pilch DR, Orr AH, Ivanova VS, Bonner WM. DNA double-stranded breaks induce histone H2AX phosphorylation on serine 139. J Biol Chem. 1998;273:5858-5868. PMID: 9488723
- 15. Rogakou EP, Nieves-Neira W, Boon C, Pommier Y, Bonner WM. Initiation of DNA fragmentation during apoptosis induces phosphorylation of H2AX histone at serine 139. J Biol Chem. 2000;275:9390-9395. PMID: 10734083
- 16. Paull TT, Rogakou EP, Yamazaki V, Kirchgessner CU, Gellert M, Bonner WM. A critical role for histone H2AX in recruitment of repair factors to nuclear foci after DNA damage. Curr Biol. 2000;10:886-895. PMID: 10959836
- 17. Zhang R, Kang KA, Piao MJ, Ko DO, Wang ZH, Chang WY, You HJ, Lee IK, Kim BJ, Kang SS, Hyun JW. Preventive effect of 7,8-dihydroxyflavone against oxidative stress induced genotoxicity. Biol Pharm Bull. 2009;32:166-171. PMID: 19182370
- 18. Piao MJ, Kang KA, Zhang R, Ko DO, Wang ZH, You HJ, Kim HS, Kim JS, Kang SS, Hyun JW. Hyperoside prevents oxidative damage induced by hydrogen peroxide in lung fibroblast cells via an antioxidant effect. Biochim Biophys Acta. 2008;1780(:1448-1457. PMID: 18761393
- 19. Feng R, Ma H, Hassig CA, Payne JE, Smith ND, Mapara MY, Hager JH, Lentzsch S. KD5170, a novel mercaptoketone-based histone deacetylase inhibitor, exerts antimyeloma effects by DNA damage and mitochondrial signaling. Mol Cancer Ther. 2008;7:1494-1505. PMID: 18566220
- 20. Shin JS, Kang KA, Kim ES, Zhang R, Piao MJ, Ko DO, Wang ZH, Maeng YH, Eun SY, Chae S, Chung HS, Hyun JW. Cytoprotective activity of annphenone against oxidative stress-induced apoptosis in V79-4 lung fibroblast cells. Cell Biol Int. 2008;32:1099-1107. PMID: 18550394
- 21. Ksiazek K, Passos JF, Olijslagers S, Saretzki G, Martin-Ruiz C, von Zglinicki T. Premature senescence of mesothelial cells is associated with non-telomeric DNA damage. Biochem Biophys Res Commun. 2007;362:707-711. PMID: 17720141
- 22. Crowe SL, Movsesyan VA, Jorgensen TJ, Kondratyev A. Rapid phosphorylation of histone H2A.X following ionotropic glutamate receptor activation. Eur J Neurosci. 2006 May;23(9):2351-2361. PMID: 16706843
- 23. Vasko MR, Guo C, Kelley MR. The multifunctional DNA repair/redox enzyme Ape1/Ref-1 promotes survival of neurons after oxidative stress. DNA Repair (Amst). 2005;4:367-379. PMID: 15661660
- 24. Kim JS, Krasieva TB, Kurumizaka H, Chen DJ, Taylor AM, Yokomori K. Independent and sequential recruitment of NHEJ and HR factors to DNA damage sites in mammalian cells. J Cell Biol. 2005;170:341-347. PMID: 16061690
- 25. Ismail IH, Hendzel MJ. The gamma-H2A.X: is it just a surrogate marker of double-strand breaks or much more? Environ Mol Mutagen. 2008;49:73-82. PMID: 18095327
- 26. Das AK, Sato M, Story MD, Peyton M, Graves R, Redpath S, Girard L, Gazdar AF, Shay JW, Minna JD, Nirodi CS. Non-small-cell lung cancers with kinase domain mutations in the epidermal growth factor receptor are sensitive to ionizing radiation. Cancer Res. 2006;66:9601-9608. PMID: 17018617
- 27. Beretta GL, Zunino F. Relevance of extracellular and intracellular interactions of camptothecins as determinants of antitumor activity. Biochem Pharmacol. 2007;74(10):1437-1444. PMID: 17540344
- 28. Montecucco A, Biamonti G. Cellular response to etoposide treatment. Cancer Lett. 2007;252(1):9-18. PMID: 17166655

Warranty

Millipore Corporation ("Millipore") warrants its products will meet their applicable published specifications when used in accordance with their applicable instructions for a period of one year from shipment of the products. **MILLIPORE MAKES NO OTHER WARRANTY, EXPRESSED OR IMPLIED. THERE IS NO WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** The warranty provided herein and the data, specifications and descriptions of Millipore products appearing in Millipore's published catalogues and product literature may not be altered except by express written agreement signed by an officer of Millipore. Representations, oral or written, which are inconsistent with this warranty or such publications are not authorized and if given, should not be relied upon.

In the event of a breach of the foregoing warranty, Millipore's sole obligation shall be to repair or replace, at its option, the applicable product or part thereof, provided the customer notifies Millipore promptly of any such breach. If after exercising reasonable efforts, Millipore is unable to repair or replace the product or part, then Millipore shall refund to the Company all monies paid for such applicable Product. **MILLIPORE SHALL NOT BE LIABLE FOR CONSEQUENTIAL, INCIDENTAL, SPECIAL OR ANY OTHER DAMAGES RESULTING FROM ECONOMIC LOSS OR PROPERTY DAMAGE SUSTAINED BY ANY COMPANY CUSTOMER FROM THE USE OF ITS PRODUCTS.**

(c) 2009: Millipore Corporation. All rights reserved. No part of these works may be reproduced in any form without permission in writing

Unless otherwise stated in our catalog or other company documentation accompanying the product(s), our products are intended for research use only and are not to be used for any other purpose, which includes but is not limited to, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses or any type of consumption or application to humans or animals.

This page is blank intentionally.