



MOUSE ANTI-(H)-RAS MONOCLONAL ANTIBODY

CATALOG NUMBER:	MAB3291	QUANTITY:	100 µg
LOT NUMBER:		CONCENTRATION:	1 mg/mL
CLONE NAME:	7D7.2	ISOTYPE:	IgG _{2b}
SPECIFICITY:	Recognizes H-Ras (the oncogene of Harvey murine sarcoma virus). Approximate molecular weight of 21 kDa.		
IMMUNOGEN:	Full-length recombinant human H-Ras – GST fusion protein		
APPLICATIONS:	Western blot ELISA <i>Optimal working dilutions must be determined by end user.</i>		
SPECIES REACTIVITY:	Mouse		
FORMAT:	Purified immunoglobulin		
PRESENTATION:	0.02M phosphate buffer, 0.25M NaCl, pH 7.6, 0.1% sodium azide		
STORAGE/HANDLING:	Maintain refrigerated at 2-8°C in undiluted aliquots for up to 6 months.		
WARNING:	This reagent contains 0.1% sodium azide as preservative. Due to potential hazards arising from the build up of this material in pipes, spent reagent should be disposed of with liberal volumes of water.		

Important Note: *During shipment, small volumes of product will occasionally become entrapped in the seal of the product vial. For products with volumes of 200 µL or less, we recommend gently tapping the vial on a hard surface or briefly centrifuging the vial in a tabletop centrifuge to dislodge any liquid in the container's cap.*

**FOR RESEARCH USE ONLY; NOT FOR USE IN DIAGNOSTIC
PROCEDURES. NOT FOR HUMAN OR ANIMAL CONSUMPTION**

Unless otherwise stated in our catalog or other company documentation accompanying the product(s), our products are intended for research use only and are not to be used for any other purpose, which includes but is not limited to, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses or any type of consumption or application to humans or animals.



©1999 - 2011: Millipore Corporation. All rights reserved. No part of these works may be reproduced in any form without permission in writing.