

Plate Location	Catalog Number	Product Name	Alternate Name	Concentration	Cell-Permeable	Reversible	ATP-Competitive	Purity	CAS Number
A1	<a href="#">116890</a>	Adenosine Kinase Inhibitor	4-Amino-5-(3-bromophenyl)-7-(6-morpholino-pyridin-3-yl)pyrido[2,3-d]pyrimidine, 2HCl	10 mM	Yes	Yes	Yes	92.02% by HPLC	214697-26-4
A2	<a href="#">124029</a>	Akt Inhibitor XII, Isozyme-Selective, Akti-2	1-((2-(4-((4-(2,3-Dihydro-2-oxo-1H-benzimidazol-1-yl)-1-piperidinyl)methyl)phenyl)-3-phenyl-6-quinoxalinyloxy)carbonyl)-4-methyl-piperazine, 3HCl and 1-((3-(4-((4-(2,3-Dihydro-2-oxo-1H-benzimidazol-1-yl)-1-piperidinyl)methyl)phenyl)-2-phenyl-6-quinoxalinyloxy)carbonyl)-4-methyl-piperazine, 3HCl	10 mM	Yes	Yes	No	97.05% by HPLC (mixture of regioisomers)	
A3	<a href="#">181305</a>	Arcyriaflavin A, Synthetic		10 mM	Yes	Yes	Yes	98.44% by HPLC	
A4	<a href="#">191500</a>	1-Azakenpaullone	1-AKP	10 mM	Yes	Yes	Yes	96.55% by HPLC	676596-65-9

A5	<a href="#">203294</a>	Bisindolylmaleimide III, Hydrochloride	2-[1-(3-Aminopropyl)-1H-indol-3-yl]-3-(1H-indol-3-yl)maleimide, HCl	10 mM	Yes	Yes	Yes	98.34% by HPLC	
A6	<a href="#">203303</a>	Bisindolylmaleimide V	2,3-bis(1H-Indol-3-yl)-N-methylmaleimide	10 mM	Yes	Yes	Yes	97.99% by HPLC	113963-68-1
A7	<a href="#">203881</a>	CR8, (R)-Isomer	2-(R)-(1-Ethyl-2-hydroxyethylamino)-6-(4-(2-pyridyl)benzyl)-9-isopropylpurine	10 mM	Yes	Yes	Yes	98.52% by HPLC	
A8	<a href="#">203882</a>	CR8, (S)-Isomer	2-(S)-(1-Ethyl-2-hydroxyethylamino)-6-(4-(2-pyridyl)benzyl)-9-isopropylpurine	10 mM	Yes	Yes	Yes	99.15% by HPLC	

A9	<a href="#">208922</a>	CaMKII Inhibitor, CK59	2-(2-Hydroxyethylamino)-6-aminohexylcarbamic acid <i>tert</i> -butyl ester-9-isopropylpurine	10 mM	Yes	Yes	Yes	99.85% by HPLC	140651-18-9
A10	<a href="#">217699</a>	Cdk1 Inhibitor IV, RO-3306		10 mM	Yes	Yes	Yes	99.93% by HPLC	
A11	<a href="#">217707</a>	Cdc7/Cdk9 Inhibitor	2-(Pyridin-4-yl)-1,5,6,7-tetrahydro-4H-pyrrolo[3,2-c]pyridinone	10 mM	Yes	Yes	Yes	99.83% by HPLC	
A12	BLANK								
B1	<a href="#">218697</a>	Casein Kinase II Inhibitor I	4,5,6,7-Tetrabromobenzotriazole	10 mM	Yes	Yes	Yes	99.29% by HPLC	17374-26-4
B2	<a href="#">218699</a>	Casein Kinase II Inhibitor II, DMAT	2-Dimethylamino-4,5,6,7-tetrabromo-1H-benzimidazole	10 mM	Yes	Yes	Yes	99.93% by HPLC	749234-11-5
B3	<a href="#">218713</a>	Keratinocyte Differentiation Inducer	3-(3-(2-(3,4,5-Trimethoxy-phenylamino)-7H-pyrrolo[2,3-d]pyrimidin-7-yl)phenyl)propionitrile	10 mM	Yes	Yes	Yes	94.75% by HPLC	

B4	<a href="#">219445</a>	Cdk2 Inhibitor II	Compound 3	10 mM	Yes	Yes	Yes	96.94% by HPLC (sum of two isomers)	
B5	<a href="#">219448</a>	Cdk2/5 Inhibitor	N <sup>4</sup> -(6-Aminopyrimidin-4-yl)-sulfanilamide, HCl	10 mM	Yes	Yes	Yes	99.93% by HPLC	
B6	<a href="#">219457</a>	Cdk Inhibitor, p35	2-(3-Hydroxypropylamino)-6-(o-hydroxybenzylamino)-9-isopropylpurine	10 mM	Yes	Yes	Yes	99.26% by HPLC	
B7	<a href="#">220485</a>	Chk2 Inhibitor	5-(2-Amino-5-oxo-1,5-dihydroimidazol-4-ylidene)-3,4,5,10,2H-azepino[3,4-b]indol-1-one	10 mM	Yes	Yes	Yes	99.63% by HPLC	724708-21-8
B8	<a href="#">234501</a>	Compound 401	2-(Morpholin-1-yl)pyrimido[2,1-a]isoquinolin-4-one	10 mM	Yes	Yes	Yes	99.56% by HPLC	168425-64-7

B9	<a href="#">238806</a>	Cdk2/9 Inhibitor	(4-(2-Amino-4-methylthiazol-5-yl)pyrimidin-2-yl)-(3-nitrophenyl)amine	10 mM	Yes	Yes	Yes	95.76% by HPLC	
B10	<a href="#">238811</a>	Cdk9 Inhibitor II	4-(3,5-Diamino-1H-pyrazol-4-ylazo)-phenol	10 mM	Yes	Yes	Yes	99.62% by HPLC	140651-18-9
B11	<a href="#">238900</a>	4-Cyano-3-methylisoquinoline		10 mM	Yes	Yes	Yes	100% by HPLC	
B12	BLANK								
C1	<a href="#">324515</a>	eEF-2 Kinase Inhibitor, NH125	1-Benzyl-3-cetyl-2-methylimidazolium iodide	10 mM	Yes	Yes	Yes	>97% by NMR	278603-08-0
C2	<a href="#">361556</a>	GSK-3 Inhibitor IX, Control, MeBIO	1-Methyl-BIO	10 mM	Yes	Yes	Yes	99.91% by HPLC	

C3	<a href="#">365252</a>	Gö 7874, Hydrochloride		5 mM	Yes	Yes	Yes	98.80% by HPLC	
C4	<a href="#">371958</a>	H-8, Dihydrochloride	N-[2-(Methylamino)ethyl]-5-isoquinolinesulfonamide, 2HCl	10 mM	Yes	Yes	Yes	100% by HPLC	113276-94-1
C5	<a href="#">371964</a>	HA 1004, Dihydrochloride	N-(2-Guanidinoethyl)-5-isoquinolinesulfonamide, 2HCl	10 mM	Yes	Yes	Yes	98.94% by HPLC	92564-34-6
C6	<a href="#">401482</a>	IKK-2 Inhibitor V	N-(3,5-Bis-trifluoromethylphenyl)-5-chloro-2-hydroxybenzamide	10 mM	Yes	Yes		98.79% by HPLC	978-62-1
C7	<a href="#">401483</a>	IKK-2 Inhibitor VI	(5-Phenyl-2-ureido)thiophene-3-carboxamide	10 mM	Yes	Yes	Yes	99.71% by HPLC	

C8	<a href="#">401486</a>	IKK Inhibitor VII		10 mM	Yes	Yes	Yes	98.44% by HPLC	
C9	<a href="#">401487</a>	IKK-2 Inhibitor VIII	2-Amino-6-(2-(cyclopropylmethoxy)-6-hydroxyphenyl)-4-(4-piperidiny)-3-pyridinecarbonitrile	10 mM	Yes	Yes	Yes	97.40% by HPLC	
C10	<a href="#">401488</a>	IKK-3 Inhibitor IX	5-(5,6-Dimethoxybenzimidazol-1-yl)-3-(2-methanesulfonyl-benzyloxy)-thiophene-2-carbonitrile	10 mM	Yes	Yes	Yes	98.53% by HPLC	
C11	<a href="#">401489</a>	IKK Inhibitor X	N-(6-Chloro-9H- $\beta$ -carbolin-8-yl)nicotinamide	10 mM	Yes	Yes	Yes	99.59% by HPLC	
C12	BLANK								

D1	<a href="#">401490</a>	IKK-2 Inhibitor XI	(5-Phenyl-3-ureido)-thiophene-2-carboxamide	10 mM	Yes	Yes	Yes	99.46% by HPLC	
D2	<a href="#">402086</a>	Iridubin-3'-monoxime, 5-Iodo-		10 mM	Yes	Yes	Yes	97.75% by HPLC	
D3	<a href="#">406170</a>	IP3K Inhibitor	N <sup>2</sup> -( <i>m</i> -Trifluorobenzyl), N <sup>6</sup> -( <i>p</i> -nitrobenzyl)purine	10 mM	Yes	Yes	Yes	98.82% by HPLC	519178-28-0
D4	<a href="#">407900</a>	5-Iodotubercidin	4-Amino-5-iodo-7-(β-D-ribofuranosyl)pyrrolo[2,3-d]pyrimidine	10 mM	Yes	Yes	Yes	96.75% by HPLC	24386-93-4
D5	<a href="#">420320</a>	KT5720		5 mM	Yes	Yes	Yes	99.18% by HPLC	108068-98-0



D6	<a href="#">422709</a>	KN-92	2-[N-(4-Methoxybenzenesulfonyl)]amino-N-(4-chlorocinnamyl)-N-methylbenzylamine, Phosphate	10 mM	NA	NA	NA	99.75% by HPLC	
D7	<a href="#">440206</a>	LY 294002, 4'-NH <sub>2</sub>	2-(4-Morpholinyl)-8-(4-aminophenyl)-4H-1-benzopyrone-4-one	10 mM	Yes	Yes	Yes	99.66% by HPLC	942289-87-4
D8	<a href="#">444965</a>	MEK1/2 Inhibitor II	N-Cyclopropylmethoxy-3,4,5-trifluoro-2-(4-iodo-2-methylphenylamino)benzamide	10 mM	Yes	Yes	No	98.43% by HPLC	212631-61-3
D9	<a href="#">475864</a>	MK-2 Inhibitor III	2-(2-Quinolin-3-ylpyridin-4-yl)-1,5,6,7-tetrahydro-4H-pyrrolo-[3,2-c]pyridin-4-one	10 mM	Yes	Yes	Yes	98.81% by HPLC	
D10	<a href="#">475880</a>	ML-7, Hydrochloride	1-(5-Iodonaphthalene-1-sulfonyl)homopiperazine, HCl	10 mM	Yes	Yes	Yes	99.24% by HPLC	110448-33-4

D11	<a href="#">480065</a>	Necrostatin-1	5-(Indol-3-ylmethyl)-(2-thio-3-methyl)hydantoin	10 mM	Yes	Yes	Yes	95.70% by HPLC	4311-88-0
D12	BLANK								
E1	DMSO								
E2	<a href="#">495621</a>	Olomoucine II	6-(2-Hydroxybenzylamino)-2-((1R)-(hydroxymethyl)propyl)amino)-9-isopropylpurine	10 mM	Yes	Yes	Yes	95.51% by HPLC	
E3	<a href="#">506106</a>	p21-Activated Kinase Inhibitor III, IPA-3	2,2';-Dihydroxy-1,1'-dinaphthyldisulfide	10 mM	Yes	Yes	No	99.00% by HPLC	
E4	<a href="#">506153</a>	p38 MAP Kinase Inhibitor IV	2,2'-Sulfonyl-bis-(3,4,6-trichlorophenol)	10 mM	Yes	Yes	Yes	95.58% by HPLC	1638-41-1
E5	<a href="#">506157</a>	p38 MAP Kinase Inhibitor VI, JX401	N-(2-Methoxy-4-thiomethyl)benzoyl-4-benzylpiperidine	10 mM	Yes	Yes	No	98.74% by HPLC	349087-34-9

E6	<a href="#">506158</a>	p38 MAP Kinase Inhibitor VII, SD-169	Indole-5-carboxamide	10 mM	Yes	Yes	Yes	98.67% by HPLC	1670-87-7
E7	<a href="#">506163</a>	p38 MAP Kinase Inhibitor VIII	(4-((2-Amino-4-bromophenyl)amino)-2-chlorophenyl)-(2-methylphenyl)methanone	10 mM	Yes	Yes	Yes	99.18% by HPLC	321351-00-2
E8	<a href="#">524611</a>	PIKfyve Inhibitor	6-Amino-N-(3-(4-(4-morpholinyl)pyrido[3';2':4,5]furo[3,2-d]pyrimidin-2-yl)phenyl)-3-pyridine carboxamide	10 mM	Yes	Yes	Yes	99.90% by HPLC	371942-69-7
E9	<a href="#">526520</a>	PIM1 Kinase Inhibitor II	3-Cyano-4-phenyl-6-(3-bromo-6-hydroxy)phenyl-2(1H)-pyridone	10 mM	Yes	Yes	Yes	90.40% by HPLC	
E10	<a href="#">526522</a>	PIM1 Kinase Inhibitor IV	4-(3-(4-Chlorophenyl)-2,1-benzisoxazol-5-yl)-2-pyrimidinamine	10 mM				99.35% by HPLC	
E11	<a href="#">526523</a>	PIM1/2 Kinase Inhibitor V	(Z)-5-(3-Trifluoromethylbenzylidene)thiazolidine-2,4-dione	10 mM	Yes	Yes	Yes	99.86% by HPLC	
E12	BLANK								
F1	DMSO								

F2	<a href="#">526524</a>	PIM1/2 Kinase Inhibitor VI	(Z)-5-(4-Propoxybenzylidene)thiazolidine-2,4-dione	10 mM	Yes	Yes	Yes	99.48% by HPLC	
F3	<a href="#">528111</a>	PI 3-K $\alpha$ Inhibitor IV	3-(4-Morpholinothieno[3,2-d]pyrimidin-2-yl)phenol, 2HCl	10 mM	Yes	Yes	Yes	99.54% by HPLC	
F4	<a href="#">528112</a>	PI 3-K $\gamma$ /CKII Inhibitor	(5-(4-Fluoro-2-hydroxyphenyl)furan-2-ylmethylene)thiazolidine-2,4-dione	10 mM	Yes	Yes	Yes	95.93% by HPLC	
F5	<a href="#">528113</a>	PI 3-K $\beta$ Inhibitor VI, TGX-221	( $\pm$ )-7-Methyl-2-(morpholin-4-yl)-9-(1-phenylaminoethyl)-pyrido[1,2-a]-pyrimidin-4-one	10 mM	Yes	Yes	Yes	99.23% by HPLC	663619-89-4
F6	<a href="#">528114</a>	PI 3-K $\gamma$ Inhibitor VII	5-(Benzo[1,3]dioxol-5-ylmethylene)-thiazolidine-2,4-dione	10 mM	Yes	Yes	Yes	99.78% by HPLC	

F7	<a href="#">528116</a>	PI 3-Ka Inhibitor VIII	N-((1E)-(6-Bromoimidazo[1,2-a]pyridin-3-yl)methylene)-N'-methyl-N''-(2-methyl-5-nitrobenzene)sulfonylhydrazide, HCl	10 mM	Yes	Yes	Yes	97.25% by HPLC	
F8	<a href="#">528282</a>	Polo-like Kinase Inhibitor I	5-(5,6-Dimethoxybenzimidazol-1-yl)-3-(4-methanesulfonyl-benzyloxy)-thiophene-2-carboxamide	10 mM	Yes	Yes	Yes	99.19% by HPLC	
F9	<a href="#">528283</a>	Polo-like Kinase Inhibitor II, BTO-1	5-Cyano-7-nitro-2-(benzothiazolo-N-oxide)-carboxamide	10 mM	Yes	Yes	Yes	98.09% by HPLC	40647-02-7
F10	<a href="#">539644</a>	UCN-01	7-Hydroxystaurosporine	5 mM	Yes	Yes	Yes	95.64% by HPLC	112953-11-4

F11	<a href="#">551590</a>	Quercetagenin	3,3',4',5,6,7-Hexahydroxyflavone	10 mM	Yes	Yes	Yes	98.02% by HPLC	90-18-6
F12	BLANK								
G1	DMSO								
G2	<a href="#">553509</a>	Ras/Rac Transformation Blocker, SCH 51344	6-Methoxy-4-(2-((2-hydroxyethoxy)-ethyl)amino)-3-methyl-1H-pyrazolo[3,4-b]quinoline	10 mM	Yes	Yes		98.96% by HPLC	171927-40-5
G3	<a href="#">554717</a>	Reversine	2-(4-Morpholinoanilino)-6-cyclohexylaminopurine	10 mM	Yes	Yes	Yes	96.93% by HPLC	656820-32-5
G4	<a href="#">555550</a>	Rho Kinase Inhibitor	(S)-(+)-2-Methyl-1-[(4-methyl-5-isoquinoliny)sulfonyl]homopiperazine, 2HCl	10 mM	Yes	Yes	Yes	98.74% by HPLC	
G5	<a href="#">555551</a>	Rho Kinase Inhibitor II	N-(4-Pyridyl)-N'-(2,4,6-trichlorophenyl)urea	10 mM	Yes	Yes	Yes	99.92% by HPLC	
G6	<a href="#">555555</a>	Rho Kinase Inhibitor V	N-(4-(1H-pyrazol-4-yl)phenyl)-2,3-dihydrobenzo[b][1,4]dioxine-2-carboxamide	10 mM	Yes	Yes	Yes	99.03% by HPLC	





G7	<a href="#">557360</a>	Roscovitine	2-(R)-(1-Ethyl-2-hydroxyethylamino)-6-benzylamino-9-isopropylpurine	10 mM	Yes	Yes	Yes	99.88% by HPLC	186692-46-6
G8	<a href="#">557362</a>	Roscovitine, (S)-Isomer	2-(S)-(1-Ethyl-2-hydroxyethylamino)-6-benzylamino-9-isopropylpurine	10 mM	Yes	Yes	Yes	99.49% by HPLC	
G9	<a href="#">557520</a>	Ro-31-8220	3-[1-[3-(Amidinothio)propyl-1H-indol-3-yl]-3-(1-methyl-1H-indol-3-yl)maleimide	10 mM	Yes	Yes	Yes	99.21% by HPLC	138489-18-6
G10	<a href="#">559285</a>	RSK Inhibitor, SL0101	Kaempferol-3-O-(3",4"-di-O-acetyl- $\alpha$ -L-rhamnopyranoside)	10 mM	Yes	Yes	Yes	97.26% by HPLC	





G11	<a href="#">559399</a>	SB 203580, Sulfone	4-(4-Fluorophenyl)-2-(4-methylsulfonylphenyl)-5-(4-pyridyl)-1H-imidazole	10 mM	Yes	Yes	Yes	99.59% by HPLC	152121-46-5
G12	BLANK								
H1	DMSO								
H2	<a href="#">559404</a>	SB 239063	<i>trans</i> -1-(4-Hydroxycyclohexyl)-4-(4-fluorophenyl)-5-(2-methoxypyrimidin-4-yl)imidazole	10 mM	Yes	Yes	Yes	99.61% by HPLC	
H3	<a href="#">565715</a>	Scytonemin, <i>Lyngbya</i> sp.	SCY	10 mM	Yes	Yes	Mixed Type	92.32% by HPLC	
H4	<a href="#">569615</a>	Stem-Cell Factor/c-Kit Inhibitor, ISCK03	4- <i>t</i> -Butylphenyl-N-(4-imidazol-1-yl-phenyl)sulfonamide	10 mM	Yes	Yes		99.39% by HPLC	
H5	<a href="#">570100</a>	Ste11 MAPKKK Activation Inhibitor	4-((2,4-Dichlorophenyl)amino)-6,7-dimethoxyquinazoline	10 mM	Yes	Yes		99.71% by HPLC	










H6	<a href="#">616404</a>	Tpl2 Kinase Inhibitor II	4-(Cycloheptylamino)-6-(pyridin-3-yl-methylamino)-3-cyano-[1,7]-naphthyridine, hydrate	10 mM	Yes	Yes	Yes	97.94% by HPLC	
H7	<a href="#">655203</a>	TX-1918	2-((3,5-dimethyl-4-hydroxyphenyl)-methylene)-4-cyclopentene-1,3-dione	10 mM	Yes	Yes	No	97.62% by HPLC	
H8	<a href="#">681500</a>	WHI-P180, Hydrochloride	4-(3'-Hydroxyphenyl)amino-6,7-dimethoxyquinazoline, HCl	10 mM	Yes	Yes	Yes	97.76% by HPLC	211555-08-7
H9	<a href="#">681637</a>	Wee1/Chk1 Inhibitor	4-(2-Phenyl)-9-hydroxypyrrolo[3,4-c]carbazole-1,3-(2H,6H)-dione	10 mM	Yes	Yes	Yes	97.14% by HPLC	
H10	<a href="#">681640</a>	Wee1 Inhibitor	4-(2-Chlorophenyl)-9-hydroxypyrrolo[3,4-c]carbazole-1,3-(2H,6H)-dione	10 mM	Yes	Yes	Yes	99.76% by HPLC	













Molecular Formula	Molecular Weight	Structure	Pubchem SID Number	Human Kinome Branch	
$C_{22}H_{19}BrN_6O \cdot 2HCl$	536.3		<a href="#">26758156</a>	Other	
$C_{39}H_{39}N_7O_2 \cdot 3HCl$	747.2		<a href="#">56364532</a>	AGC	
$C_{20}H_{11}N_3O_2$	325.3		<a href="#">26758250</a>	CMGC	
$C_{15}H_{10}BrN_3O$	328.2		<a href="#">26758278</a>	CMGC	






$C_{23}H_{20}N_4O_2 \cdot HCl$	420.9	 <chem>C1=CN(C1CCCCN)C2=C(C3=CC=CC=C3N)C(=O)NC(=O)C4=CC=CC=C4N</chem> ·HCl	<a href="#">26758308</a>	AGC	
$C_{21}H_{15}N_3O_2$	341.3	 <chem>CN1C(=O)C2=C(C3=CC=CC=C3N)C(=O)N1C4=CC=CC=C4N</chem>	<a href="#">26758310</a>	AGC	
$C_{24}H_{29}N_7O$	431.5	 <chem>CC(O)C1=NC2=C(N1)N(C)N(C2)N3CCN(C3)C4=CC=CC=C4N5CCNCC5</chem>	<a href="#">58097335</a>	CMGC	
$C_{24}H_{29}N_7O$	431.5	 <chem>CC(O)C1=NC2=C(N1)N(C)N(C2)N3CCN(C3)C4=CC=CC=C4N5CCNCC5</chem>	<a href="#">81058714</a>	CMGC	

$C_{21}H_{37}N_7O_3$	435.6		<a href="#">56365459</a>	CAMK	
$C_{18}H_{13}N_3OS_2$	351.5		<a href="#">26758397</a>	CMGC	
$C_{12}H_{11}N_3O$	213.2		<a href="#">81055074</a>	CMGC	
$C_6HBr_4N_3$	434.7		<a href="#">26758402</a>	CMGC	
$C_9H_7Br_4N_3$	476.8		<a href="#">26758403</a>	CMGC	
$C_{24}H_{23}N_5O_3$	429.5		<a href="#">56365458</a>	CMGC	












$C_{14}H_{11}BrN_4O_3S$	395.2		<a href="#">26758435</a>	CMGC	
$C_{10}H_{11}N_5O_2S \cdot HCl$	301.8		<a href="#">26758436</a>	CMGC	
$C_{18}H_{24}N_6O_2$	356.4		<a href="#">26758437</a>	CMGC	
$C_{15}H_{13}N_5O_2$	295.3		<a href="#">26758461</a>	CAMK	
$C_{16}H_{15}N_3O_2$	281.3		<a href="#">56365462</a>	Atypical	






$C_{14}H_{12}N_6O_2S$	328.4		<a href="#">26758511</a>	CMGC	
$C_9H_{10}N_6O$	218.2		<a href="#">26758512</a>	CMGC	
$C_{11}H_8N_2$	168.2		<a href="#">26758513</a>	AGC	
$C_{27}H_{45}IN_2$	524.6		<a href="#">81055075</a>	Atypical	
$C_{17}H_{12}BrN_3O_2$	370.2		<a href="#">26758809</a>	CMGC	






$C_{27}H_{26}N_4O_4 \cdot HCl$	507		<a href="#">26758819</a>	AGC	
$C_{12}H_{15}N_3O_2S \cdot 2HCl$	338.3		<a href="#">26758854</a>	AGC	
$C_{12}H_{15}N_5O_2S \cdot 2HCl$	366.3		<a href="#">26758859</a>	AGC	
$C_{15}H_8ClF_6NO_2$	383.7		<a href="#">26758930</a>	Other	
$C_{12}H_{11}N_3O_2S$	261.3		<a href="#">26758931</a>	Other	














$C_{28}H_{29}N_5OS$	483.6		<a href="#">26758934</a>	Other	
$C_{21}H_{24}N_4O_2$	364.4		<a href="#">26758935</a>	Other	
$C_{22}H_{19}N_3O_5S_2$	469.5		<a href="#">81055077</a>	Other	
$C_{17}H_{11}ClN_4O$	322.8		<a href="#">81055076</a>	Other	





$C_{12}H_{11}N_3O_2S$	261.3		<a href="#">58097340</a>	Other	
$C_{16}H_{10}IN_3O_2$	403.2		<a href="#">26758940</a>	CMGC	
$C_{20}H_{16}F_3N_7O_2$	443.4		<a href="#">26758949</a>	Other	
$C_{11}H_{13}IN_4O_4$	392.2		<a href="#">26758970</a>	Other	
$C_{32}H_{31}N_3O_5$	537.6		<a href="#">26759011</a>	AGC	







$C_{24}H_{25}ClN_2O_3S \cdot H_3PO_4$	555		<a href="#">26759025</a>	NA	
$C_{19}H_{18}N_2O_3$	322.4		<a href="#">57287545</a>	Other	
$C_{18}H_{16}F_3IN_2O_2$	476.2		<a href="#">56421977</a>	STE	
$C_{21}H_{16}N_4O \cdot H_2O$	358.4		<a href="#">57269231</a>	STE	
$C_{15}H_{17}IN_2O_2S \cdot HCl$	452.7		<a href="#">26759187</a>	CAMK	

$C_{13}H_{13}N_3OS$	259.3		<a href="#">26759223</a>	TKL	
$C_{19}H_{26}N_6O_2$	370.5		<a href="#">26759292</a>	CMGC	
$C_{20}H_{14}O_2S_2$	350.5		<a href="#">57269235</a>	STE	
$C_{12}H_4Cl_6O_4S$	456.9		<a href="#">58097342</a>	STE	
$C_{21}H_{25}NO_2S$	355.5		<a href="#">81055078</a>	STE	





$C_9H_8N_2O$	160.2		<a href="#">57269236</a>	STE	
$C_{20}H_{16}BrClN_2O$	415.7		<a href="#">57287541</a>	STE	
$C_{25}H_{21}N_7O_3$	467.5		<a href="#">81055079</a>	Other	
$C_{18}H_{11}BrN_2O_2$	367.2		<a href="#">81055080</a>	CAMK	
$C_{17}H_{11}ClN_4O$	322.1		<a href="#">56459315</a>	CAMK	
$C_{11}H_6F_3NO_2S$	273.2		<a href="#">81055081</a>	CAMK	






$C_{13}H_{13}NO_3S$	263.3		<a href="#">81055082</a>	CAMK	
$C_{16}H_{15}N_3O_2S \cdot 2HCl$	386.3		<a href="#">26759375</a>	Other	
$C_{14}H_8FNO_4S$	305.3		<a href="#">26759376</a>	Other CMGC	
$C_{21}H_{24}N_4O_2$	364.4		<a href="#">81055083</a>	Other	
$C_{11}H_7NO_4S$	249.2		<a href="#">56365803</a>	Other	






$C_{16}H_{14}N_5O_4SBr \cdot HCl \cdot 2H_2O$	524.8		<a href="#">81055084</a>	Other	
$C_{22}H_{21}N_3O_6S_2$	487.6		<a href="#">81055085</a>	Other	
$C_9H_4N_4O_4S$	264.2		<a href="#">58097343</a>	Other	
$C_{28}H_{26}N_4O_4$	482.5		<a href="#">81055086</a>	AGC CAMK CMGC TK	


$C_{15}H_{10}O_8$	318.3		<a href="#">26759427</a>	CAMK	
$C_{16}H_{20}N_4O_3$	316.4		<a href="#">26759438</a>	Other	
$C_{21}H_{27}N_7O$	393.5		<a href="#">26759441</a>	STE Other	
$C_{16}H_{21}N_3O_2S \cdot 2HCl$	392.3		<a href="#">26759444</a>	AGC	
$C_{12}H_8Cl_3N_3O$	316.6		<a href="#">26759445</a>	AGC	
$C_{18}H_{15}N_3O_3$	321.3		<a href="#">81055087</a>	AGC	



$C_{19}H_{26}N_6O$	354.5		<a href="#">26759456</a>	CMGC	
$C_{19}H_{26}N_6O$	354.5		<a href="#">26759457</a>	CMGC	
$C_{25}H_{23}N_5O_2S \cdot CH_4O_3S$	553.7		<a href="#">26759466</a>	AGC CMGC	
$C_{25}H_{24}O_{12}$	516.5		<a href="#">81058712</a>	AGC	

$C_{21}H_{16}FN_3O_2S$	393.4		<a href="#">26759484</a>	CMGC	
$C_{20}H_{21}FN_4O_2$	368.4		<a href="#">26759488</a>	CMGC	
$C_{36}H_{20}N_{20}^4$	544.6		<a href="#">26759499</a>	AGC CAMK CMGC Other	
$C_{19}H_{21}N_3O_2S$	355.5		<a href="#">81058713</a>	TK	
$C_{16}H_{13}Cl_2N_3O_2$	350.2		<a href="#">81058715</a>	TK	

$C_{22}H_{24}N_6 \cdot H_2O$	390.5		<a href="#">57287543</a>	STE	
$C_{14}H_{12}O_3$	228.2		<a href="#">26759674</a>	Atypical	
$C_{16}H_{15}N_3O_3$	297.3		<a href="#">57269238</a>	CMGC	
$C_{20}H_{12}N_2O_3 \cdot H_2O$	346.3		<a href="#">26759753</a>	Other CAMK	
$C_{20}H_{11}ClN_2O_3$	362.8		<a href="#">26759754</a>	Other	

$C_{24}H_{19}ClN_2O_3$	418.9		<a href="#">26759755</a>	Other	