



Product Information

Protein Phosphatase 2A Inhibitor Protein, 2- β human, recombinant
expressed in *E. coli*

Product Number **P 2368**
Storage Temperature $-70\text{ }^{\circ}\text{C}$

Synonyms: $I_2\beta^{PP2A}$; I_2^{PP2A}

Product Description

Human Protein Phosphatase 2A Inhibitor Protein, 2- β ($I_2\beta^{PP2A}$) is a recombinant, human protein expressed in *E. coli*. It is a potent, heat-stable PP2A inhibitor with a molecular mass of approximately 41 kDa.

This protein inhibits all forms of PP2A with a k_i of approximately 0.1 nM with myelin basic protein, histone H1, and other substrates, but not with casein. PP2A is inhibited by this protein in a manner noncompetitive with the substrate and it is considered specific for PP2A. $I_2\beta^{PP2A}$ has been determined to be the equivalent of the acute undifferentiated leukemia-associated SET protein (also termed PHAP-II and TAF-1 α). Additionally, $I_2\beta^{PP2A}$ has been shown to act as an activator of c-Jun and AP-1 directed gene expression.¹ $I_2\beta^{PP2A}$ is primarily located in the nucleus of most mammalian cell types. $I_2\beta^{PP2A}$ differs from $I_2\alpha^{PP2A}$ by a distinct difference in the nucleotide sequence exhibited in the N-terminal region of the protein.²

PP2A is a major mammalian protein serine/threonine phosphatase involved in the regulation of diverse cellular processes. This regulation is effected through control of signaling pathways by a mechanism of phosphorylation/dephosphorylation with a variety of protein kinases. Importantly, PP2A is believed to play a role in the regulation of NF- κ B signaling, which has been shown to promote cell survival and escape from apoptosis.²

This product is supplied as a solution of 50 M Tris-HCl, pH 7.0, containing 14 mM 2-mercaptoethanol, 1 mM benzamidine, 0.1 mM PMSF, 1 mM EDTA, 0.1% BRIJ[®] 35, and 10% glycerol.

Purity: minimum 90% (SDS-PAGE)

Precautions and Disclaimer

This product is for laboratory use only. Please consult the Material Data Safety Sheet for information regarding hazards and safe handling practices.

Storage/Stability

The product ships on dry ice and it is recommended to store the product at $-70\text{ }^{\circ}\text{C}$. After thawing, store stock solutions as aliquots at $-70\text{ }^{\circ}\text{C}$. Avoid repeated freeze-thaw cycles.

References

1. Al-Murrani, S.W.K., et al., Expression of I_2^{PP2A} , an inhibitor of protein phosphatase 2A, induces c-Jun and AP-1 activity. *Biochem. J.*, **341**, 293-298 (1999).
2. Nagata, K., et al., Replication factor encoded by a putative oncogene, *set*, associated with myeloid leukemogenesis. *Proc. Natl. Acad. Sci.*, **92**, 4279-4283 (1995).
3. Saito, S., et al., Functional domains of template-activating-factor-I as a protein phosphatase 2A inhibitor. *Biochem. Biophys. Res. Commun.*, **259**, 471-475 (1999).
4. Okuwaki, M., and Nagata, K., Template activating factor-I remodels the chromatin structure and stimulates transcription from the chromatin template. *J. Biol. Chem.*, **273**, 34511-34518 (1998).
5. Khang, H.S., and Choi, I., Protein phosphatase 2A modulated the proliferation of human multiple myeloma cells via regulation for the production of reactive oxygen intermediates and anti-apoptotic factors. *Cell Immuno.*, **213**, 34-44 (2001).
6. Klumpp, S., and Kriegstein, J., Serine/threonine protein phosphatases in apoptosis. *Curr. Opin. Pharmacol.*, **2**, 458-462 (2002).

7. Li, M., et al., Purification and characterization of two potent heat-stable protein inhibitors of protein phosphatase 2A from bovine kidney. *Biochemistry*, **34**, 1988-1996 (1995).

8. Yang, J., et al., Protein phosphatase 2A interacts with and directly dephosphorylates RelA. *J. Biol. Chem.*, **276**, 47828-47833 (2001).

BRIJ is a registered trademark of the ICI Group.

JBB/MAM 8/02

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.