

## Product Information

**Monoclonal Anti-CD8-PE, clone UCHT-4**  
produced in mouse, purified immunoglobulin

Catalog Number **P5560**

### Product Description

Monoclonal Anti-CD8 (mouse IgG2a isotype) is derived from the hybridoma produced by the fusion of mouse myeloma cell line NS-1 and splenocytes from Balb/c mice immunized with human thymocytes followed by peripheral blood T cells. The isotype is determined by a double diffusion assay using Mouse Monoclonal Antibody Isotyping Reagents, Catalog No. ISO2. The product is prepared by conjugation of R-Phycoerythrin (R-PE) with purified CD8 monoclonal antibody. The conjugate is then purified by gel filtration to remove unbound R-PE and antibody. No free R-PE or free antibody is detectable.

Monoclonal Anti-CD8 recognizes the CD8 30/32 kDa human T cytotoxic/suppressor lymphocytes surface glycoprotein. The CD8 antigen is strongly expressed on approximately one-third of mature T cells (cytotoxic/suppressor T cells). In suspension about 90% of thymocytes will be stained while cortical and medullar sections of thymus will also show staining. A subset of NK cells express this antigen somewhat weakly. Monoclonal Anti-CD8 does not stain B lymphocytes, monocytes or granulocytes. The epitope recognized by this clone is sensitive to routine formalin fixation and paraffin embedding. Cryostat sections post fixed in formalin can also be stained. Note: In order to obtain best results in different preparations, it is recommended that each individual user determine their optimum working dilutions by titration assay.

Monoclonal Anti-CD8 may be used for:

- Enumeration of total T cytotoxic/suppressor lymphocytes in bone marrow, blood and other body fluids.
- Identification and localization of T cytotoxic/suppressor lymphocytes in lymphoid and other tissues.
- Analysis of cell mediated cytotoxicity.
- Studies of immunoregulation in health and disease.
- Investigation of NK cells.

### Components/Reagents

Supplied as a solution in 0.01 M phosphate buffered saline, pH 7.4, containing 1% BSA and 0.1% sodium azide as a preservative.

### Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

### Storage/Stability

Store at 2-8 °C. Protect from prolonged exposure to light. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use.

### Procedure

Note: In order to obtain best results in different preparations, it is recommended that each individual user determine their optimum working dilutions by titration assay.

### Reagents and materials needed but not supplied

1. Whole human blood collected by standard clinical blood evacuation tubes with EDTA, ACD-A or heparin anticoagulant **or**
2. Human cell suspension (e.g., peripheral blood mononuclear cells isolated on HISTOPAQUE® (Product No. 1077-1)).
3. Diluent: 0.01M phosphate buffered saline (PBS), pH 7.4, containing 1% BSA and 0.1% NaN<sub>3</sub>.
4. PE conjugated, isotype-matched, non-specific mouse immunoglobulin (negative control, Product No. P 4810
5. 12 x 75 mm test tubes.
6. Adjustable micropipet.
7. Centrifuge.
8. Counting chamber.
9. Trypan Blue (Product No. T 0776), 0.2% in 0.01 M PBS, pH 7.4.
10. 2% paraformaldehyde in PBS.
11. Whole blood lysing solution
12. Flow cytometer.

### Direct Immunofluorescent Staining

1.
  - a. Use 100  $\mu$ l of whole blood **or**
  - b. Adjust cell suspension to  $1 \times 10^7$  cells/ml in diluent. Cells should be >90% viable as determined by dye exclusion (e.g., Trypan Blue). For each sample, add 100  $\mu$ l or  $1 \times 10^6$  cells per tube.
2. Add 10  $\mu$ l of conjugate to tube(s) containing cells to be stained. Vortex tube gently. Incubate the cells at room temperature (18 – 22 °C) for 30 minutes. Proper controls to be included for each sample are:
  - a. An autofluorescence control: 10  $\mu$ l diluent in place of monoclonal antibody, followed by steps 3 - 7.
  - b. A negative staining control: 10  $\mu$ l of PE conjugated, isotype-matched non-specific mouse immunoglobulin ( Product No. P 4810) at the same concentration as test antibody followed by steps 3 - 7.
3.
  - a. If whole blood is used, use lysing solution after incubation according to manufacturer's instructions.
  - b. If a mononuclear cell suspension is used, proceed to Step. 4.
4. Add 2 ml of diluent to all tubes.
5. Pellet cells by centrifugation at 500 x g for 10 minutes.
6. Remove supernatant by careful aspiration.
7. Resuspend cells in 0.5 ml of 2% paraformaldehyde. Analyze in a flow cytometer according to manufacturer's instructions.

### Controls

It is advisable to run the appropriate negative controls. Negative controls establish background fluorescence and non-specific binding of the primary and secondary antibodies. The ideal negative control reagent is a mouse monoclonal or myeloma protein that has no reactivity with human cells. It should be matched to the isotype of the antibody and at the same concentration and F/P molar ratio as the antibody. The degree of autofluorescence or negative control reagent fluorescence will vary with the type of cells under study and the sensitivity of the instrument used.

### **Product Profile**

When assayed by flow cytometric analysis, using 10  $\mu$ l of the conjugate to stain  $1 \times 10^6$  cells a fluorescence intensity is observed similar to that obtained with saturating monoclonal antibody levels. The percent population positive is also at the maximum percentage positive using saturating monoclonal antibody levels.

### **References**

1. Fischer, A., et al., *Immunology*, **48**, 177 (1983).
2. Pozilly, P., et al., *Diabetes*, **32**, 91 (1983).
3. Rowe, D., et al., *Clin. Exp. Immunol.*, **54**, 327 (1983).
4. Lwin, K. Y., et al., *Int. J. Cancer*, **36**, 433 (1985).
5. Merckenschlager, M., et al., *Eur. J. Immunol.*, **18**, 1653 (1988).
6. Merckenschlager, M., and Beverly, P. C., *Int. Immunol.*, **1**, 450 (1989).
7. Leucocyte Typing IV, Knapp, W., et al., (Eds.), p. 1076 (Oxford Press, New York, 1989).
8. Reinherz, E. L., et al., *J. Immunol.*, **124**, 1301 (1980).
9. Reinherz, E. L., et al., *Nature*, **294**, 168 (1981).
10. Biddison, W. E., et al., *Hum. Immunol.*, **9**, 117 (1984).
11. Kavanthas, P., et al., *Proc. Nat. Acad. Sci. USA*, **81**, 7688 (1984).
12. Martin, P. J., et al., *J. Immunol.*, **132**, 759 (1984).
13. Littman, D. R., et al., *Cell*, **40**, 237 (1985).
14. Barber, E. K., et al., *Proc. Nat. Acad. Sci. USA*, **86**, 3277 (1989).

AH,PHC 09/10-1

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply.

Please see reverse side of the invoice or packing slip.